



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **S1250C0 12" 50LB BLK Strnoghhold CBL Tie** *Panduit Corporation*

Catalog Number	S1250C0
Manufacturer	Panduit Corporation
Description	The S12-50-C0 Stronghold Cable Ties Offers Contractors An Economical Cable Tie Option For Commercial Construction and General-Purpose Applications. Standard, 11.81" (300MM) Length and Are Ah-2 Plenum Rated. For Outdoor Use, Made Of Weather Resistant Nylon 6.6, Are Black In Color and Come In Packages Of 100.
Weight per unit	0.4600 (lbs/each)
Product Category	Cable Ties & Wraps

### **Features**

media	Yes
Tensile Strength	50

### **Dimensions and Weight**

Length	11.8
Thickness	0.06

### **Descriptions**

Description	12" 50LB BLK STRNOGHOLD CBL TIE
extra long description	PAN S12-50-C0 StrongHold™ S12-50-C0
Long Description	The S12-50-C0 StrongHold Cable Ties offers contractors an economical cable tie option for commercial construction and general-purpose applications. Standard, 11.81" (300mm) length and are AH-2 Plenum rated. For outdoor use, made of Weather Resistant Nylon 6.6, are black in color and come in packages of 100.
Product Type	Stronghold™ S12-50-C0 Cable Tie, Black, Pa 6.6, 50LB Min Loo
Special Features	Plenum

### **Manufacturer Information**

Brand	Panduit®
GTIN	00613056258143
Manufacturers Part Number	S12-50-C0
UPC	613056258143

### **Taxonomies, Classifications, and Categories**

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Cable Tie



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Availability

minimum qty	100
-------------	-----

## Packaging

Carton	100
--------	-----

Package	1000
---------	------

Weight Per each	0.46
-----------------	------

## Uses, Certifications, and Standards

standard	UL 62275 Compliant (Type 2, 21), RoHS Compliant
----------	---