



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PS60SSAX 60A 600VAC N/F Safety Switch W/Aux.

*Pass & Seymour/Legrand*

Catalog Number	PS60SSAX
Manufacturer	Pass & Seymour/Legrand
Description	Non-Fusible Safety Switch With Auxillary Contact. 60 Amp, 600 Vac.
Weight per unit	4.4 (lbs/each)
Product Category	Non-Fusible Disconnect Safety

### Features

action	Motor Disconnect Switch
actuator	Switch Handle
amperage rating	60
connection	Hard Wired
Contact Configuration	1 N.O. & 1 N.C.
Contact Rating	10A @ 600VAC
insulation	Complies with NEMA 4X
Material	Valox 357®
operating cycles	Mechanical: 15,000 Cycles; Electrical: 10,000 Cycles
Poles	4
Switch Type	Switch Handle
Voltage Rating	600

### Dimensions and Weight

Height	12.38
Size	7.19 L x 6.31 W x 12.38 H
Width	6.31

### Descriptions

Description	60A 600VAC N/F SAFETY SWITCH W/AUX.
extra long description	P&S PS60SSAX 60A 600VAC N/F SAFETY
Long Description	Non-Fusible Safety Switch with Auxillary Contact. 60 amp, 600 vac.
Product Type	60A 600VAC N/F Safety Switch W/Aux.
Special Features	Compact design fits in most I-beams to provide mounting versatility, easy access, and reduced possibility of impact damage. Nonconductive, watertight, corrosion-, heat-, and impact-resistant Valox® enclosure ensures NEMA 4X and 12 ratings and withstands the harshest industrial environments. Corrosion-resistant, stainless steel captive screws speeds installation, minimize risk of lost parts, and withstand abuse. Adjustable mounting feet can be moved to center of unit for instant strut- or pole-mounting with



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007150131
Manufacturers Part Number	PS60SSAX
sub brand	Pass & Seymour
UPC	785007150131

## Taxonomies, Classifications, and Categories

Category Description	Residential GFCI devices
Type	Non-Fusible Safety Switch with Auxiliary Contact

## Packaging

Carton	1
Weight Per each	4.35

## Uses, Certifications, and Standards

Application	Industrial
Enclosure	NEMA Type 4X (watertight, hosedown), Type 12K (dusttight, falling dirt); IP67 Suitability
environmental conditions	Moisture Resistance: Per UL50, Section 35, NEMA Enclosure Type 4X (watertight, hosedown), Type 12K (dusttight, falling dirt), and IP67 suitability; Flammability: UL94 5VA and VO Classification; UV Resistance: All enclosure materials are UV stable
Frequency Rating	60
Mounting	External adjustable feet with five (5) positions. Can be mounted directly to channel or strut (no washers required).
Operating Temperature	Maximum continuous: +60C; Minimum continuous: -50C without impact
standard	UL, CSA