

# S29841 A19 LED

## 9.8A19/OMNI/220/LED/35K/GU24

Lamp Type	LED
Bulb Type	A19
Base Type	GU24
Wattage	9.8
Color Temperature	3500
Color Rendering Index CRI	80
Warranty	3 Year Limited



### Lighting Facts Per Bulb

Brightness	800 lumens
Estimated Energy Cost	\$1.08
per year, based on 3 hrs/day, 11c/kWh. Energy cost depends on utility rates and light use.	
Average Life	22.8 years
Based on 3 hrs/day	
Light Appearance	
Energy Used	9 watts

## Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S29841	LED	*20045923298411	120	9.8	60	A19	GU24
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
GU24	9.8A19/OMNI/220/LED/35K/GU24	Yes	n/a	4 3/16	2 3/8	800	25000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
3500	Neutral White	80	220	24	Box	Yes	Yes

# S29841 A19 LED

## 9.8A19/OMNI/220/LED/35K/GU24

Lamp Type	LED
Bulb Type	A19
Base Type	GU24
Wattage	9.8
Color Temperature	3500
Color Rendering Index CRI	80
Warranty	3 Year Limited



### Lighting Facts Per Bulb

<b>Brightness</b>	<b>800 lumens</b>
<b>Estimated Energy Cost</b>	<b>\$1.08</b>
per year, based on 3 hrs/day, 11c/kWh. Energy cost depends on utility rates and light use.	
<b>Average Life</b>	<b>22.8 years</b>
Based on 3 hrs/day	
<b>Light Appearance</b>	
<b>Energy Used</b>	<b>9 watts</b>

## Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S29841	LED	*20045923298411	120	9.8	60	A19	GU24
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
GU24	9.8A19/OMNI/220/LED/35K/GU24	Yes	n/a	4 3/16	2 3/8	800	25000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
3500	Neutral White	80	220	24	Box	Yes	Yes