

Eaton S811+V50P3S

Catalog Number: S811+V50P3S

Eaton S811+ soft starter, 500 A, V-frame, Premium, 600 V rated, Level/Edge Sense, Three-pole, 24 V power, 47-63 Hz, 1-2 conductors, #2/0 AWG to 500 kcmil wire, 120 Vdc, 240 Vac, Modbus RTU, NEMA 0, LCD display, -30°C to -50°C



General specifications

Product Name

Eaton S811+ soft starter

Catalog Number

S811+V50P3S

UPC

786685559148

Product Length/Depth

7.39 in

Product Height

16.57 in

Product Width

11.05 in

Product Weight

103 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

CE Marked

Certifications

EN 60947-4-2
UL Listed
CSA file No. 3211-06
IEC 60947-4-2
UL Recognized
CSA Certified for Elevator Duty

Catalog Notes

All units require a 24 Vdc power supply found on catalog Page V6-T1-85, or equivalent., S811+T_, S811+U_ and

S811+V_ units require lug kits,

S811+U50_ unit does not have IEC

ce defaultTaxonomyAttributeLabel

Amperage Rating

500A

Display material

LCD

AC current - max

240 Vac

DC current - max

120 Vdc

Number Of Poles

Three-pole

Type

Soft starter

Frequency rating

47-63 Hz

Used with

Three-phase motors

Power supply

24 V

Frame size

V

Options

Level/edge sense

Pump control and extended ramp

Inline or inside-the-delta wiring configuration

600V rated

Premium

Operating temperature - max

50 °C

Communication

Modbus RTU

Configuration

Inline (default) or inside the delta

NEMA rating

NEMA 0

Size

NEMA 0

Operating voltage

200-600 V

Wire size

#2/0 AWG-500 kcmil

Module interface

Digital interface module

Operating temperature - min

-30 °C

Resources

Application notes

S8x1 adjustment - Switching from S801+ to S811+

Brochures

S811+/S801+ soft starters

Catalogs

Product Datasheet - S811+V50P3S

Eaton's Volume 6—Solid-State Motor Control

Product Range Catalog Drives Engineering

Drawings

Type S811+ Soft Starter - V-frame

Installation instructions

Instructions for S811+ Soft Starter, S811+T..., S811+U..., and S811+V

Multimedia

Soft Starter DS7 up to 32 A

Soft starter DS7 up to 200 A

Soft Starter Product Family Overview

Specifications and datasheets

Eaton Specification Sheet - S811+V50P3S



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Eaton S811+V50P3S

Catalog Number: S811+V50P3S

Eaton S811+ soft starter, 500 A, V-frame, Premium, 600 V rated, Level/Edge Sense, Three-pole, 24 V power, 47-63 Hz, 1-2 conductors, #2/0 AWG to 500 kcmil wire, 120 Vdc, 240 Vac, Modbus RTU, NEMA 0, LCD display, -30°C to -50°C



General specifications

Product Name

Eaton S811+ soft starter

UPC

786685559148

Product Height

16.57 in

Product Weight

103 lb

Compliances

CE Marked

Catalog Number

S811+V50P3S

Product Length/Depth

7.39 in

Product Width

11.05 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

EN 60947-4-2

UL Listed

CSA file No. 3211-06

IEC 60947-4-2

UL Recognized

CSA Certified for Elevator Duty

Catalog Notes

All units require a 24 Vdc power supply found on catalog Page V6-T1-85, or equivalent., S811+T_, S811+U_ and

S811+V_ units require lug kits,

S811+U50_ unit does not have IEC

ce defaultTaxonomyAttributeLabel

Amperage Rating

500A

Display material

LCD

AC current - max

240 Vac

DC current - max

120 Vdc

Number Of Poles

Three-pole

Type

Soft starter

Frequency rating

47-63 Hz

Used with

Three-phase motors

Power supply

24 V

Frame size

V

Options

Level/edge sense

Pump control and extended ramp

Inline or inside-the-delta wiring configuration

600V rated

Premium

Operating temperature - max

50 °C

Communication

Modbus RTU

Configuration

Inline (default) or inside the delta

NEMA rating

NEMA 0

Size

NEMA 0

Operating voltage

200-600 V

Wire size

#2/0 AWG-500 kcmil

Module interface

Digital interface module

Operating temperature - min

-30 °C

Resources

Application notes

S8x1 adjustment - Switching from S801+ to S811+

Brochures

S811+/S801+ soft starters

Catalogs

Product Datasheet - S811+V50P3S

Eaton's Volume 6—Solid-State Motor Control

Product Range Catalog Drives Engineering

Drawings

Type S811+ Soft Starter - V-frame

Installation instructions

Instructions for S811+ Soft Starter, S811+T..., S811+U..., and S811+V

Multimedia

Soft Starter DS7 up to 32 A

Soft starter DS7 up to 200 A

Soft Starter Product Family Overview

Specifications and datasheets

Eaton Specification Sheet - S811+V50P3S



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia