



GE
Lighting

24929 - GE Q300T3CL/PRO-6PK

Q300T3CL/PRO-6PK

Product Photo



GENERAL CHARACTERISTICS

| | |
|--------------------------|----------------------------|
| Rated Life Hours-nominal | 2000 h |
| Primary Application | Standard <General Purpose> |
| Product Technology | Halogen |
| Bulb Shape | T2.5 |

PHOTOMETRIC CHARACTERISTICS

| | |
|--------------------------------|---------|
| Nominal Initial Lumen per Watt | 19 |
| Initial Lumens-nominal | 5760 lm |
| Color Temperature | 2900 K |

PRODUCT INFORMATION

| | |
|----------------------------------|------------------|
| Product Code | 24929 |
| Description | Q300T3CL/PRO-6PK |
| Alternative Unit Of Measure | EACH |
| Standard Package Quantity | 144 |
| Ean UPC | 043168249294 |
| Standard Package GTIN | 00043168249294 |
| No Of Items Per Sales Unit | 1 |
| No Of Items Per Standard Package | 144 |
| Sales Unit | Each |
| UCC | 043168249294 |
| Alternative Unit Of Measure | CASE |

ELECTRICAL CHARACTERISTICS

| | |
|---------------------|-------|
| Input Voltage [nom] | 120 V |
| Rated power (Watts) | 300 W |



GE
Lighting

24929 - GE Q300T3CL/PRO-6PK

Q300T3CL/PRO-6PK

Product Photo



GENERAL CHARACTERISTICS

| | |
|--------------------------|----------------------------|
| Rated Life Hours-nominal | 2000 h |
| Primary Application | Standard <General Purpose> |
| Product Technology | Halogen |
| Bulb Shape | T2.5 |

PHOTOMETRIC CHARACTERISTICS

| | |
|--------------------------------|---------|
| Nominal Initial Lumen per Watt | 19 |
| Initial Lumens-nominal | 5760 lm |
| Color Temperature | 2900 K |

PRODUCT INFORMATION

| | |
|----------------------------------|------------------|
| Product Code | 24929 |
| Description | Q300T3CL/PRO-6PK |
| Alternative Unit Of Measure | EACH |
| Standard Package Quantity | 144 |
| Ean UPC | 043168249294 |
| Standard Package GTIN | 00043168249294 |
| No Of Items Per Sales Unit | 1 |
| No Of Items Per Standard Package | 144 |
| Sales Unit | Each |
| UCC | 043168249294 |
| Alternative Unit Of Measure | CASE |

ELECTRICAL CHARACTERISTICS

| | |
|---------------------|-------|
| Input Voltage [nom] | 120 V |
| Rated power (Watts) | 300 W |