



## POWER OUTLET RECEPTACLE OPENINGS, ONE GANG, 302/304 STAINLESS STEEL

SS724 | [Pass & Seymour](#)

### FEATURES & BENEFITS

One Gang Power Outlet Receptacle Opening, 2.156" hole for 2.125" diameter device - 2 mtg. holes, Smooth 302/304 Metal.



- Type 302/304 Stainless Steel, non-magnetic: .032" nominal thickness.
- Brushed finish.
- This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion.
- Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist.
- Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.
- Packaged in protective film, with finish-matching screws.
- Variety of special plated finishes.
- Paintable to match plastic plates.
- Can be silk-screened or engraved, and custom punched with over 300 opening styles.

### SPECIFICATIONS

#### GENERAL INFO

Size: Standard  
Type: Single

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: Yes  
CUL Listing No: No  
cULus: No  
cURus: No  
Federal Spec: No

UL Listing No: Yes  
UN SPSC: 39121704  
UR: No

#### **DIMENSIONS**

Diameter (US): 2.156" Hole

#### **TECHNICAL INFORMATION**

Material: 302/304 Stainless Steel  
Capacity: 1-gang

#### **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: UNITED STATES OF AMERICA  
Buy American Act Status: Buy American Act Compliant

