

# Eaton SVX125A1-4A1N1

Catalog Number: SVX125A1-4A1N1

Eaton SVX adjustable frequency drive, 125HP, NEMA Type 1/IP21, 480V, FR8, Three-phase, EMC H, Standard Software, A/N keypad, No brake chopper, Standard boards



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton SVX adjustable frequency drive	SVX125A1-4A1N1
<b>UPC</b>	<b>Product Length/Depth</b>
782116011599	13.5 in
<b>Product Height</b>	<b>Product Width</b>
30.1 in	11.5 in
<b>Product Weight</b>	<b>Warranty</b>
127 lb	2 year
<b>Compliances</b>	<b>Certifications</b>
Contact Manufacturer	IEC 61800-2
	UL 508C
	EN 61800-3 Level H

## defaultTaxonomyAttributeLabel

### Brake chopper

No brake chopper

### Modification

Standard boards

### Horsepower

125 hp

### Frame size

8

### Keypad

Alphanumeric

### Input

EMC H

Three-phase

### Rating

NEMA 1, IP21

### Software

Standard

## Resources

### Application notes

[Electromagnetic compatibility \(EMC\)](#)

[Connecting drives to generator supplies](#)

[SPL - Variable frequency drives with a common DC bus](#)

### Brochures

[SVX9000 Adjustable Frequency Drives Brochure](#)

[SVX9000 Adjustable Frequency Drives Product Aid](#)

### Catalogs

[Eaton's Volume 6—Solid-State Motor Control](#)

[Product Datasheet - SVX125A1-4A1N1](#)

[Product Range Catalog Drives Engineering](#)

### Drawings

[SVX\\_\(FR8\) 3D Inventor](#)

[SVX\\_\(FR8\) AutoCAD 2D Footprint \(mm\)](#)

[SVX\\_\(FR8\) 2D PDF](#)

[SVX\\_\(FR8\) 2D Drawing Xchange](#)

[SVX\\_\(FR8\) 3D Model Xchange](#)

[SVX and SPX Series FR4-FR11 PDF Open Drawings](#)

[SVX\\_\(FR8\) AutoCAD 2D Footprint](#)

### Installation instructions

[9000X AFD User Manual](#)

### Specifications and datasheets

[Eaton Specification Sheet - SVX125A1-4A1N1](#)

# Eaton SVX125A1-4A1N1

Catalog Number: SVX125A1-4A1N1

Eaton SVX adjustable frequency drive, 125HP, NEMA Type 1/IP21, 480V, FR8, Three-phase, EMC H, Standard Software, A/N keypad, No brake chopper, Standard boards



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton SVX adjustable frequency drive	SVX125A1-4A1N1
<b>UPC</b>	<b>Product Length/Depth</b>
782116011599	13.5 in
<b>Product Height</b>	<b>Product Width</b>
30.1 in	11.5 in
<b>Product Weight</b>	<b>Warranty</b>
127 lb	2 year
<b>Compliances</b>	<b>Certifications</b>
Contact Manufacturer	IEC 61800-2
	UL 508C
	EN 61800-3 Level H

## defaultTaxonomyAttributeLabel

### Brake chopper

No brake chopper

### Modification

Standard boards

### Horsepower

125 hp

### Frame size

8

### Keypad

Alphanumeric

### Input

EMC H

Three-phase

### Rating

NEMA 1, IP21

### Software

Standard

## Resources

### Application notes

[Electromagnetic compatibility \(EMC\)](#)

[Connecting drives to generator supplies](#)

[SPL - Variable frequency drives with a common DC bus](#)

### Brochures

[SVX9000 Adjustable Frequency Drives Brochure](#)

[SVX9000 Adjustable Frequency Drives Product Aid](#)

### Catalogs

[Eaton's Volume 6—Solid-State Motor Control](#)

[Product Datasheet - SVX125A1-4A1N1](#)

[Product Range Catalog Drives Engineering](#)

### Drawings

[SVX\\_\(FR8\) 3D Inventor](#)

[SVX\\_\(FR8\) AutoCAD 2D Footprint \(mm\)](#)

[SVX\\_\(FR8\) 2D PDF](#)

[SVX\\_\(FR8\) 2D Drawing Xchange](#)

[SVX\\_\(FR8\) 3D Model Xchange](#)

[SVX and SPX Series FR4-FR11 PDF Open Drawings](#)

[SVX\\_\(FR8\) AutoCAD 2D Footprint](#)

### Installation instructions

[9000X AFD User Manual](#)

### Specifications and datasheets

[Eaton Specification Sheet - SVX125A1-4A1N1](#)