



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



T50L9M4 Cable Tie, 15", UI Rated, 50LB TS *Hellermannntyton*

Catalog Number	T50L9M4
Manufacturer	Hellermannntyton
Description	T-Series Cable Ties Feature Inside Serrations to Provide A Positive Hold On Wire and Cable Bundles. The Head Design Guarantees High Tensile Strength and A Low Insertion Force. The Bent Tail Design Allows Quick and Simple Installations By Hand. For High-Volume Applications, Tensioning Tools Are Available to Ensure Consistent and Safe Installation.
Weight per unit	0.0052 (lbs/each)
Product Category	Cable Ties & Wraps

Features

Material	Plastic
----------	---------

Dimensions and Weight

Length	15.350000000000000;389.8900
Width	0.180000000000000;4.5720

Descriptions

Description	CABLE TIE, 15", UL RATED, 50LB TS
extra long description	TYN T50L9M4 T50L NAT TIE 15.4"
Long Description	T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.
Product Type	T50L Nat Tie 15.4"
Special Features	Standard Cable Tie, 15.4" Long, 50lb Tensile Strength, PA66, Natural, 1000/pkg

Manufacturer Information

Brand	Hellermannntyton
GTIN	04031026274720
Manufacturers Part Number	T50L9M4
UPC	089306084570

Taxonomies, Classifications, and Categories

Category Description	WIRE LUBE, MARKERS, & TIES
Type	T50L



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1000
Package	5000
Weight Per each	0.0052

Uses, Certifications, and Standards

Application	Used to bundle and secure wire and cable.
standard	UL Listed (US and Canada), UL Recognized (US and Canada)