

**DESCRIPTION**

The Halo RA4 LED Adjustable Gimbal series are retrofit LED Modules for 4" aperture recessed downlights. The RA4 gimbals feature adjustment of 35-degree tilt and up to 360-degree rotation. In addition the RA4 gimbals offer selection of narrow flood (NFL) and very wide flood (VWFL) models for beam distributions suitable for accent, task, grazing and general area lighting. The RA4 integral LED 120V driver is dimmable with most leading edge and trailing edge phase control dimmers.

**SPECIFICATION FEATURES****MECHANICAL**

- Module includes LED, heat sink, reflector, lens optic, baffle reveal, and trim ring
- Durable die-cast aluminum construction
- Integrated heat sink design conducts heat away from the LED keeping the junction temperatures below specified maximums, even when installed in insulated ceiling environments
- Halo matte white paint finish
- 35-degree tilt
- Up to 360-degree rotation

**Optics****NARROW FLOOD - NFL**

- Precision acrylic lens
- Optical design creates a clean, uniform 25-degree beam distribution

**VERY WIDE FLOOD - VWFL**

- Impact-resistant polycarbonate
- Convex form for lamp-like appearance
- Diffusing, wide beam for even illumination

**MOUNTING****Friction Blades**

- Precision formed spring blades secure module with friction fit to compatible housings.
- Friction blade design allows the RA4 to be installed in any position within the housing aperture (360 degrees)

**Housing Compatibility**

See Housing Compatibility

**LED**

- Color Temperature (CCT)  
Options: 2700K, 3000K
- Color Rendering Index (CRI) 90
- LED is a chip on board design consisting of a multiple LED package with proximity phosphor coating to create one virtual white light source for a productive "cone of light"

**ELECTRICAL****Power Connections**

- LED connector is a non-screw base luminaire disconnect offering easy installation with the matching Halo H995 Series housings.
- LED Connector meets high-efficacy luminaire requirements for a non-screw base socket, and where required to qualify as a high-efficacy luminaire. (California Title-24)
- The included E26 medium screw-base Edison adapter provides easy retrofit of incandescent housings (see Housing Compatibility).

**Ground Connection**

- Separate grounding cable included on the module for attachment to the housing during installation.

**LED Driver**

- Dimmable driver is a 120 Volt, high efficiency, electronic power supply providing DC power to the LED.
- Driver meets FCC EMI/RFI Consumer Level limits for use in residential and commercial installations.
- Driver features high power factor, low THD, and has integral thermal protection in the event of over temperature or internal failure.
- Driver mounts externally to the module, allowing future replacement, if needed.

**Dimming**

- The Halo RA4 LED is designed for dimming capability to 10% in normal operation with standard 120V leading edge (LE) and trailing edge (TE) phase control dimmers.
- The LED module may also dim to 5% nominal using dimmers with low end trim adjustment. (Consult dimmer manufacturer for dimmer details. Note, some dimmers require a neutral in the wallbox.)

**Warranty**

Cooper Lighting provides a five year limited warranty on RA56 LED.

**Compliance Labels**

- UL/cUL Listed 1598 Luminaire (with listed Halo housings)
- UL Classified (with other housings - see Housing Compatibility)
- UL/cUL Listed for Damp Location
- May be installed in housings in direct contact with air permeable insulation\*\* and combustible material
- IP ingress protection rating  
NFL models: IP25  
VWFL models: IP34

**Qualification**

- ENERGY STAR® qualified residential and commercial\*
- Can be used for State of California Title 24 high efficacy luminaire compliance\*
- Can be used for Washington State Energy Code (WSEC) and International Energy Conservation Code (IECC) high efficacy luminaire Compliance

**IC (Insulated Ceiling)**

Listed UL/cUL 1598 with compatible housings, may be used to meet insulated ceiling\*\* requirements such as:

- Washington State Energy Code (WSEC)
- International Energy Conservation Code (IECC)
- New York State Energy Conservation Construction Code (NY-ECCC)
- State of California Title 24 "Recessed Luminaires in Insulated Ceilings."

Catalog #		Type
Project		
Comments		Date
Prepared by		



**RA4 LED**  
**Very Wide Flood**  
**(VWFL)**




**RA4 LED**  
**Narrow Flood**  
**(NFL)**

**4-Inch**  
**Adjustable Gimbals**  
**All-Purpose Recessed**  
**Retrofit Modules**

**FOR USE IN INSULATED**  
**CEILING AND NON-**  
**INSULATED**  
**CEILING RATED HOUSINGS**

**HIGH EFFICACY LED**  
**WITH INTEGRAL DRIVER -**  
**DIMMABLE**



\*Qualified and compliant. Refer to ENERGY STAR® Qualified Products List and CEC (T24) Appliance Database for listings.

\*\* Not for use with housings in direct contact with spray foam insulation.

## ENERGY DATA

Minimum Starting Temp: -30°C (-22°F)

EM/RFI: FCC Title 47 CFR, Part 15, Class B (Consumer)

Sound Rating: Class A standards

Input Voltage: 120V

Power Factor: &gt;0.90

Input Frequency: 50/60Hz

THD: &lt;20%

Input Power: 10W

Input Current: 85mA

Driver-Safety Agency Approvals:

- UL60950-1 Recognized


- LPS output

- UL8750 Compliant

Maximum IC (Insulated Ceiling) Ambient Continuous Operating Temperature: 25°C (77°F)

Maximum Non-IC (NON-Insulated Ceiling) Ambient Continuous Operating Temperature 40°C (104°F)

## DIMENSIONS




## LIGHTING FACTS

## RA406927WH

2700K Source


VWFL Beam



## RA406930WH

3000K Source


VWFL Beam



## RA406927NFLWH

2700K Source


NFL Beam



## RA406930NFLWH

3000K Source

NFL Beam

For further information refer to the Lighting Facts website at <http://lightingfacts.com/>.

## ORDERING INFORMATION

**SAMPLE NUMBER:** RA406930WH

Complete unit includes RA4 LED and a compatible 4" housing; ordered separately.

RA4 Series	Accessory (order separately)
<b>Very Wide Flood - VWFL Models</b> <b>RA406927WH</b> = 4" LED Adjustable Gimbal, 90CRI, 2700K, White, Very Wide Flood <b>RA406930WH</b> = 4" LED Adjustable Gimbal, 90CRI, 3000K, White, Very Wide Flood  <b>Narrow Flood - NFL Models</b> <b>RA406927NFLWH</b> = 4" LED Adjustable Gimbal, 90CRI, 2700K, White, Narrow Flood <b>RA406930NFLWH</b> = 4" LED Adjustable Gimbal, 90CRI, 3000K, White, Narrow Flood	<b>HE26LED</b> =Replacement screw base adapter (one included with unit)

### LED Housing

Series
<b>H995ICAT</b> = 4" LED Insulated Ceiling, AIR-TITE New Construction Housing with LED luminaire connector (high efficacy compliant) <b>H995RICAT</b> = 4" LED Insulated Ceiling, AIR-TITE Remodel Housing with LED luminaire connector (high efficacy compliant)

## HOUSING COMPATIBILITY

<b>UL Listed</b> UL/cUL Listed for installation in the following Halo and All-Pro 4" recessed E26 screw based and LED dedicated housings.	All-Pro™	ET400ATSB, ET400RATSB, EI400ATSB
	Halo®	H99ICAT, H99RTAT, H99TAT, H995ICAT, H995RICAT
<b>UL Classified</b> UL Classified for retrofit in the following 4" recessed E26 screw based housings.	Utilitech	CR04ICAT
	Thomas®	PS4
	Lithonia Lighting®	L3, L3R
	Commercial Electric™	HBR2000B
	Juno®	TC1, TC1R
	Progress Lighting®	P830-TG, P832-TG

Juno®, Lithonia Lighting®, Thomas® Lighting, Progress® Lighting, Utilitech, and Commercial Electric™ and their product brand names, where identified above, are tradenames or trademarks of each respective company and Cooper Lighting makes no representations on these trademarks.

## PHOTOMETRY

**RA406927WH**

Reflector Beam Angle = VWFL Beam  
(Very Wide Flood)

CCT = 2700K

Spacing Criteria = 1.18

Lumens per Watt = 60 Lm/W

Test No. P121906


Test Model: RA406927WH

**Cone of Light Footcandles**  
0 deg Aiming Angle  
Horizontal Illuminance on Floor

Distance to Illuminated Plane	Initial Nadir Footcandles	Beam (ft.)	
		L Length	W Width
5.5'	9.7	6.4	6.4
7'	6	8.2	8.2
8'	4.6	9.4	9.4
9'	3.6	10.6	10.6
10'	2.9	11.8	11.8

**Cone of Light Footcandles**  
35 deg Aiming Angle  
Vertical Illuminance on Wall

Distance to Illuminated Plane	Initial Nadir Footcandles	Beam (ft.)		CB
		L Length	W Width	
2'	43.5	2.1	2.4	2.9
3'	19.3	3.2	3.6	4.3
4'	10.9	4.2	4.8	5.7
5'	7	5.3	6	7.1
6'	4.8	6.4	7.4	8.6
8'	2.7	8.6	9.8	11.4
10'	1.7	10.8	12.2	14.3

**Candlepower Distribution****Candela Distribution**

Degrees Vertical	Candela
0*	293
5	293
15	283
25	257
35	206
45	144
55	79
65	40
75	18
85	6
90	0

\*CBCP

**Luminance**

(Average Candela/M²)	
Degree	Avg. 0° Luminance
45	43944
55	29652
65	20532
75	15132
85	14648

**Zonal Lumen Summary**

Zone	Lumens	% Fixture
0-30	225	37.4
0-40	354	58.9
0-60	534	89.0
0-90	600	100

**RA406930WH**

Reflector Beam Angle = VWFL Beam  
(Very Wide Flood)

CCT = 3000K

Spacing Criteria = 1.18

Lumens per Watt = 61.5 Lm/W

Test No. P121908


Test Model: RA406930WH

**Cone of Light Footcandles**  
0 deg Aiming Angle  
Horizontal Illuminance on Floor

Distance to Illuminated Plane	Initial Nadir Footcandles	Beam (ft.)	
		L Length	W Width
5.5'	9.9	6.4	6.4
7'	6.1	8.2	8.2
8'	4.7	9.4	9.4
9'	3.7	10.6	10.6
10'	3	11.8	11.8

**Cone of Light Footcandles**  
35 deg Aiming Angle  
Vertical Illuminance on Wall

Distance to Illuminated Plane	Initial Nadir Footcandles	Beam (ft.)		CB
		L Length	W Width	
2'	44.6	2.1	2.4	2.9
3'	19.8	3.2	3.6	4.3
4'	11.1	4.2	4.8	5.7
5'	7.1	5.3	6	7.1
6'	5	6.4	7.4	8.6
8'	2.8	8.6	9.8	11.4
10'	1.8	10.8	12.2	14.3

**Candlepower Distribution****Candela Distribution**

Degrees Vertical	Candela
0*	301
5	300
15	290
25	263
35	211
45	147
55	81
65	41
75	19
85	6
90	0

\*CBCP

**Luminance**

(Average Candela/M²)	
Degree	Avg. 0° Luminance
45	45015
55	30407
65	21044
75	15551
85	14896

**Zonal Lumen Summary**

Zone	Lumens	% Fixture
0-30	230	37.4
0-40	362	58.9
0-60	548	89.0
0-90	615	100

## PHOTOMETRY

**RA406927NFLWH**

Reflector Beam Angle = NFL Beam  
(Narrow Flood)

CCT = 2700K

Spacing Criteria = 0.35

Lumens per Watt = 64 Lm/W

Test No. P121904

Test Model: RA406927NFLWH

**Cone of Light Footcandles**


0 deg Aiming Angle  
Horizontal Illuminance on Floor

Distance to Illuminated Plane	Initial Nadir Footcandles	Beam (ft.)	
		L Length	W Width
5.5'	98.7	1.8	1.8
7'	60.9	2.4	2.4
8'	46.6	2.8	2.8
9'	36.9	3	3
10'	29.9	3.4	3.4

**Cone of Light Footcandles**

35 deg Aiming Angle  
Vertical Illuminance on Wall

Distance to Illuminated Plane	Initial Nadir Footcandles	Beam (ft.)		CB
		L Length	W Width	
2'	168	1.7	1	2.9
3'	74.7	2.6	1.6	4.3
4'	42	3.5	2.2	5.7
5'	26.9	4.4	2.8	7.1
6'	18.7	5.3	3.4	8.6
8'	10.5	7.1	4.4	11.4
10'	6.7	8.9	5.6	14.3

**Candlepower Distribution****Candela Distribution**

Degrees Vertical	Candela
0*	2985
5	2531
15	836
25	223
35	62
45	27
55	14
65	6
75	2
85	0
90	0

**Luminance**

(Average Candela/M²)	
Degree	Avg. 0° Luminance
45	6559
55	3723
65	1726
75	577
85	168

**Zonal Lumen Summary**

Zone	Lumens	% Fixture
0-30	556	86.9
0-40	598	93.4
0-60	631	98.7
0-90	640	100

\*CBCP

**RA406930NFLWH**

Reflector Beam Angle = NFL Beam  
(Narrow Flood)

CCT = 3000K

Spacing Criteria = 0.35

Lumens per Watt = 64 Lm/W

Test No. P121905

Test Model: RA406930NFLWH

**Cone of Light Footcandles**


0 deg Aiming Angle  
Horizontal Illuminance on Floor

Distance to Illuminated Plane	Initial Nadir Footcandles	Beam (ft.)	
		L Length	W Width
5.5'	98.7	1.8	1.8
7'	60.9	2.4	2.4
8'	46.6	2.8	2.8
9'	36.9	3	3
10'	29.9	3.4	3.4

**Cone of Light Footcandles**

35 deg Aiming Angle  
Vertical Illuminance on Wall

Distance to Illuminated Plane	Initial Nadir Footcandles	Beam (ft.)		CB
		L Length	W Width	
2'	168	1.7	1	2.9
3'	74.7	2.6	1.6	4.3
4'	42	3.5	2.2	5.7
5'	26.9	4.4	2.8	7.1
6'	18.7	5.3	3.4	8.6
8'	10.5	7.1	4.4	11.4
10'	6.7	8.9	5.6	14.3

**Candlepower Distribution****Candela Distribution**

Degrees Vertical	Candela
0*	2985
5	2531
15	836
25	223
35	62
45	27
55	14
65	6
75	2
85	0
90	0

**Luminance**

(Average Candela/M²)	
Degree	Avg. 0° Luminance
45	6559
55	3723
65	1726
75	577
85	168

**Zonal Lumen Summary**

Zone	Lumens	% Fixture
0-30	556	86.9
0-40	598	93.4
0-60	631	98.7
0-90	640	100

\*CBCP

## DESCRIPTION

The Halo RA4 LED Adjustable Gimbal series are retrofit LED Modules for 4" aperture recessed downlights. The RA4 gimbals feature adjustment of 35-degree tilt and up to 360-degree rotation. In addition the RA4 gimbals offer selection of narrow flood (NFL) and very wide flood (VWFL) models for beam distributions suitable for accent, task, grazing and general area lighting. The RA4 integral LED 120V driver is dimmable with most leading edge and trailing edge phase control dimmers.

## SPECIFICATION FEATURES

### MECHANICAL

- Module includes LED, heat sink, reflector, lens optic, baffle reveal, and trim ring
- Durable die-cast aluminum construction
- Integrated heat sink design conducts heat away from the LED keeping the junction temperatures below specified maximums, even when installed in insulated ceiling environments
- Halo matte white paint finish
- 35-degree tilt
- Up to 360-degree rotation

### Optics

#### NARROW FLOOD - NFL

- Precision acrylic lens
- Optical design creates a clean, uniform 25-degree beam distribution

#### VERY WIDE FLOOD - VWFL

- Impact-resistant polycarbonate
- Convex form for lamp-like appearance
- Diffusing, wide beam for even illumination

### MOUNTING

#### Friction Blades

- Precision formed spring blades secure module with friction fit to compatible housings.
- Friction blade design allows the RA4 to be installed in any position within the housing aperture (360 degrees)

#### Housing Compatibility

See Housing Compatibility

### LED

- Color Temperature (CCT)  
Options: 2700K, 3000K
- Color Rendering Index (CRI) 90
- LED is a chip on board design consisting of a multiple LED package with proximity phosphor coating to create one virtual white light source for a productive "cone of light"

### ELECTRICAL

#### Power Connections

- LED connector is a non-screw base luminaire disconnect offering easy installation with the matching Halo H995 Series housings.
- LED Connector meets high-efficacy luminaire requirements for a non-screw base socket, and where required to qualify as a high-efficacy luminaire. (California Title-24)
- The included E26 medium screw-base Edison adapter provides easy retrofit of incandescent housings (see Housing Compatibility).

#### Ground Connection

- Separate grounding cable included on the module for attachment to the housing during installation.

#### LED Driver

- Dimmable driver is a 120 Volt, high efficiency, electronic power supply providing DC power to the LED.
- Driver meets FCC EMI/RFI Consumer Level limits for use in residential and commercial installations.
- Driver features high power factor, low THD, and has integral thermal protection in the event of over temperature or internal failure.
- Driver mounts externally to the module, allowing future replacement, if needed.

#### Dimming

- The Halo RA4 LED is designed for dimming capability to 10% in normal operation with standard 120V leading edge (LE) and trailing edge (TE) phase control dimmers.
- The LED module may also dim to 5% nominal using dimmers with low end trim adjustment. (Consult dimmer manufacturer for dimmer details. Note, some dimmers require a neutral in the wallbox.)

### Warranty

Cooper Lighting provides a five year limited warranty on RA56 LED.

### Compliance Labels

- UL/cUL Listed 1598 Luminaire (with listed Halo housings)
- UL Classified (with other housings - see Housing Compatibility)
- UL/cUL Listed for Damp Location
- May be installed in housings in direct contact with air permeable insulation\*\* and combustible material
- IP ingress protection rating  
NFL models: IP25  
VWFL models: IP34

### Qualification

- ENERGY STAR® qualified residential and commercial\*
- Can be used for State of California Title 24 high efficacy luminaire compliance\*
- Can be used for Washington State Energy Code (WSEC) and International Energy Conservation Code (IECC) high efficacy luminaire Compliance

### IC (Insulated Ceiling)

Listed UL/cUL 1598 with compatible housings, may be used to meet insulated ceiling\*\* requirements such as:

- Washington State Energy Code (WSEC)
- International Energy Conservation Code (IECC)
- New York State Energy Conservation Construction Code (NY-ECCC)
- State of California Title 24 "Recessed Luminaires in Insulated Ceilings."



**RA4 LED**  
**Very Wide Flood**  
**(VWFL)**




**RA4 LED**  
**Narrow Flood**  
**(NFL)**

**4-Inch**  
**Adjustable Gimbals**  
**All-Purpose Recessed**  
**Retrofit Modules**

**FOR USE IN INSULATED**  
**CEILING AND NON-**  
**INSULATED**  
**CEILING RATED HOUSINGS**

**HIGH EFFICACY LED**  
**WITH INTEGRAL DRIVER -**  
**DIMMABLE**



\*Qualified and compliant. Refer to ENERGY STAR® Qualified Products List and CEC (T24) Appliance Database for listings.

\*\* Not for use with housings in direct contact with spray foam insulation.



## ENERGY DATA

Minimum Starting Temp: -30°C (-22°F)

EM/RFI: FCC Title 47 CFR, Part 15, Class B (Consumer)

Sound Rating: Class A standards

Input Voltage: 120V

Power Factor: &gt;0.90

Input Frequency: 50/60Hz

THD: &lt;20%

Input Power: 10W

Input Current: 85mA

Driver-Safety Agency Approvals:

- UL60950-1 Recognized


- LPS output

- UL8750 Compliant

Maximum IC (Insulated Ceiling) Ambient Continuous Operating Temperature: 25°C (77°F)

Maximum Non-IC (NON-Insulated Ceiling) Ambient Continuous Operating Temperature 40°C (104°F)

## DIMENSIONS




## LIGHTING FACTS

## RA406927WH

2700K Source


VWFL Beam



## RA406930WH

3000K Source


VWFL Beam



## RA406927NFLWH

2700K Source


NFL Beam



## RA406930NFLWH

3000K Source

NFL Beam

For further information refer to the Lighting Facts website at <http://lightingfacts.com/>.

## ORDERING INFORMATION

**SAMPLE NUMBER:** RA406930WH

Complete unit includes RA4 LED and a compatible 4" housing; ordered separately.

RA4 Series	Accessory (order separately)
<b>Very Wide Flood - VWFL Models</b> <b>RA406927WH</b> = 4" LED Adjustable Gimbal, 90CRI, 2700K, White, Very Wide Flood <b>RA406930WH</b> = 4" LED Adjustable Gimbal, 90CRI, 3000K, White, Very Wide Flood  <b>Narrow Flood - NFL Models</b> <b>RA406927NFLWH</b> = 4" LED Adjustable Gimbal, 90CRI, 2700K, White, Narrow Flood <b>RA406930NFLWH</b> = 4" LED Adjustable Gimbal, 90CRI, 3000K, White, Narrow Flood	<b>HE26LED</b> =Replacement screw base adapter (one included with unit)

### LED Housing

Series
<b>H995ICAT</b> = 4" LED Insulated Ceiling, AIR-TITE New Construction Housing with LED luminaire connector (high efficacy compliant) <b>H995RICAT</b> = 4" LED Insulated Ceiling, AIR-TITE Remodel Housing with LED luminaire connector (high efficacy compliant)

## HOUSING COMPATIBILITY

<b>UL Listed</b> UL/cUL Listed for installation in the following Halo and All-Pro 4" recessed E26 screw based and LED dedicated housings.	All-Pro™	ET400ATSB, ET400RATSB, EI400ATSB
	Halo®	H99ICAT, H99RTAT, H99TAT, H995ICAT, H995RICAT
<b>UL Classified</b> UL Classified for retrofit in the following 4" recessed E26 screw based housings.	Utilitech	CR04ICAT
	Thomas®	PS4
	Lithonia Lighting®	L3, L3R
	Commercial Electric™	HBR2000B
	Juno®	TC1, TC1R
	Progress Lighting®	P830-TG, P832-TG

Juno®, Lithonia Lighting®, Thomas® Lighting, Progress® Lighting, Utilitech, and Commercial Electric™ and their product brand names, where identified above, are tradenames or trademarks of each respective company and Cooper Lighting makes no representations on these trademarks.



## PHOTOMETRY

**RA406927WH**

Reflector Beam Angle = VWFL Beam  
(Very Wide Flood)

CCT = 2700K

Spacing Criteria = 1.18

Lumens per Watt = 60 Lm/W

Test No. P121906


Test Model: RA406927WH

**Cone of Light Footcandles**  
0 deg Aiming Angle  
Horizontal Illuminance on Floor

Distance to Illuminated Plane	Initial Nadir Footcandles	Beam (ft.)	
		L Length	W Width
5.5'	9.7	6.4	6.4
7'	6	8.2	8.2
8'	4.6	9.4	9.4
9'	3.6	10.6	10.6
10'	2.9	11.8	11.8

**Cone of Light Footcandles**  
35 deg Aiming Angle  
Vertical Illuminance on Wall

Distance to Illuminated Plane	Initial Nadir Footcandles	Beam (ft.)		CB
		L Length	W Width	
2'	43.5	2.1	2.4	2.9
3'	19.3	3.2	3.6	4.3
4'	10.9	4.2	4.8	5.7
5'	7	5.3	6	7.1
6'	4.8	6.4	7.4	8.6
8'	2.7	8.6	9.8	11.4
10'	1.7	10.8	12.2	14.3

**Candlepower Distribution****Candela Distribution**

Degrees Vertical	Candela
0*	293
5	293
15	283
25	257
35	206
45	144
55	79
65	40
75	18
85	6
90	0

\*CBCP

**Luminance**

(Average Candela/M²)	
Degree	Avg. 0° Luminance
45	43944
55	29652
65	20532
75	15132
85	14648

**Zonal Lumen Summary**

Zone	Lumens	% Fixture
0-30	225	37.4
0-40	354	58.9
0-60	534	89.0
0-90	600	100

**RA406930WH**

Reflector Beam Angle = VWFL Beam  
(Very Wide Flood)

CCT = 3000K

Spacing Criteria = 1.18

Lumens per Watt = 61.5 Lm/W

Test No. P121908


Test Model: RA406930WH

**Cone of Light Footcandles**  
0 deg Aiming Angle  
Horizontal Illuminance on Floor

Distance to Illuminated Plane	Initial Nadir Footcandles	Beam (ft.)	
		L Length	W Width
5.5'	9.9	6.4	6.4
7'	6.1	8.2	8.2
8'	4.7	9.4	9.4
9'	3.7	10.6	10.6
10'	3	11.8	11.8

**Cone of Light Footcandles**  
35 deg Aiming Angle  
Vertical Illuminance on Wall

Distance to Illuminated Plane	Initial Nadir Footcandles	Beam (ft.)		CB
		L Length	W Width	
2'	44.6	2.1	2.4	2.9
3'	19.8	3.2	3.6	4.3
4'	11.1	4.2	4.8	5.7
5'	7.1	5.3	6	7.1
6'	5	6.4	7.4	8.6
8'	2.8	8.6	9.8	11.4
10'	1.8	10.8	12.2	14.3

**Candlepower Distribution****Candela Distribution**

Degrees Vertical	Candela
0*	301
5	300
15	290
25	263
35	211
45	147
55	81
65	41
75	19
85	6
90	0

\*CBCP

**Luminance**

(Average Candela/M²)	
Degree	Avg. 0° Luminance
45	45015
55	30407
65	21044
75	15551
85	14896

**Zonal Lumen Summary**

Zone	Lumens	% Fixture
0-30	230	37.4
0-40	362	58.9
0-60	548	89.0
0-90	615	100

## PHOTOMETRY

**RA406927NFLWH**

Reflector Beam Angle = NFL Beam  
(Narrow Flood)

CCT = 2700K

Spacing Criteria = 0.35

Lumens per Watt = 64 Lm/W

Test No. P121904

Test Model: RA406927NFLWH

**Cone of Light Footcandles**


0 deg Aiming Angle  
Horizontal Illuminance on Floor

Distance to Illuminated Plane	Initial Nadir Footcandles	Beam (ft.)	
		L Length	W Width
5.5'	98.7	1.8	1.8
7'	60.9	2.4	2.4
8'	46.6	2.8	2.8
9'	36.9	3	3
10'	29.9	3.4	3.4

**Cone of Light Footcandles**

35 deg Aiming Angle  
Vertical Illuminance on Wall

Distance to Illuminated Plane	Initial Nadir Footcandles	Beam (ft.)		CB
		L Length	W Width	
2'	168	1.7	1	2.9
3'	74.7	2.6	1.6	4.3
4'	42	3.5	2.2	5.7
5'	26.9	4.4	2.8	7.1
6'	18.7	5.3	3.4	8.6
8'	10.5	7.1	4.4	11.4
10'	6.7	8.9	5.6	14.3

**Candlepower Distribution****Candela Distribution**

Degrees Vertical	Candela
0*	2985
5	2531
15	836
25	223
35	62
45	27
55	14
65	6
75	2
85	0
90	0

**Luminance**

(Average Candela/M²)	
Degree	Avg. 0° Luminance
45	6559
55	3723
65	1726
75	577
85	168

**Zonal Lumen Summary**

Zone	Lumens	% Fixture
0-30	556	86.9
0-40	598	93.4
0-60	631	98.7
0-90	640	100

\*CBCP

**RA406930NFLWH**

Reflector Beam Angle = NFL Beam  
(Narrow Flood)

CCT = 3000K

Spacing Criteria = 0.35

Lumens per Watt = 64 Lm/W

Test No. P121905

Test Model: RA406930NFLWH

**Cone of Light Footcandles**


0 deg Aiming Angle  
Horizontal Illuminance on Floor

Distance to Illuminated Plane	Initial Nadir Footcandles	Beam (ft.)	
		L Length	W Width
5.5'	98.7	1.8	1.8
7'	60.9	2.4	2.4
8'	46.6	2.8	2.8
9'	36.9	3	3
10'	29.9	3.4	3.4

**Cone of Light Footcandles**

35 deg Aiming Angle  
Vertical Illuminance on Wall

Distance to Illuminated Plane	Initial Nadir Footcandles	Beam (ft.)		CB
		L Length	W Width	
2'	168	1.7	1	2.9
3'	74.7	2.6	1.6	4.3
4'	42	3.5	2.2	5.7
5'	26.9	4.4	2.8	7.1
6'	18.7	5.3	3.4	8.6
8'	10.5	7.1	4.4	11.4
10'	6.7	8.9	5.6	14.3

**Candlepower Distribution****Candela Distribution**

Degrees Vertical	Candela
0*	2985
5	2531
15	836
25	223
35	62
45	27
55	14
65	6
75	2
85	0
90	0

**Luminance**

(Average Candela/M²)	
Degree	Avg. 0° Luminance
45	6559
55	3723
65	1726
75	577
85	168

**Zonal Lumen Summary**

Zone	Lumens	% Fixture
0-30	556	86.9
0-40	598	93.4
0-60	631	98.7
0-90	640	100

\*CBCP