







Catalog Number: U4908-O-11GR  
Item Description: 100A RL MTR P/O  
UPC Code: 784572271951

Brand Name: Milbank  
Type: Ringless Metered Power Supply Unit  
Special Features: 4 Terminal, Plain Top, Ground Bar, No Bypass, Single Power Head, 6 Branch Circuits  
Application: Temporary Power  
Standard: UL Listed  
Voltage Rating: Up to 240 Volts Alternating Current  
Amperage Rating: 125 Ampere Continuous  
Wattage: Not Applicable  
Frequency Rating: 60 Hertz  
Phase: 1 Phase  
Number of Receptacles: 2  
Receptacle Configuration: Two NEMA 5-20 Ground Fault Receptacles  
Control: Two Single Pole 20 Ampere Breakers, No Main Breaker  
Material: G90 Galvanized Steel with Powder Coat Finish  
Mounting: Surface Mount  
Cable Size: 6 AWG to 2/0 AWG  
Enclosure: Type 3R



*Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.*

FEATURE TABLE		
ITEM	QTY	DESCRIPTION
A	4	U/L MNTG.EMBOSS
B	2	¼ SOLID K.O.
C	2	½, ¾, 1, 1¼, 1½ CONC. K.O.
D	1	¾, 1, 1¼, 1½, 2 CONC. K.O.
E	2	¼, ½, ¾, 1, 1¼, CONC. K.O.



Version:

1

All dimensions are +/- 1/16".  
 Drawing views are not to scale.  
 Utility requirements for this equipment may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.







Catalog Number: U4908-O-11GR  
Item Description: 100A RL MTR P/O  
UPC Code: 784572271951

**Brand Name:** Milbank  
**Type:** Ringless Metered Power Supply Unit  
**Special Features:** 4 Terminal, Plain Top, Ground Bar, No Bypass, Single Power Head, 6 Branch Circuits  
**Application:** Temporary Power  
**Standard:** UL Listed  
**Voltage Rating:** Up to 240 Volts Alternating Current  
**Amperage Rating:** 125 Ampere Continuous  
**Wattage:** Not Applicable  
**Frequency Rating:** 60 Hertz  
**Phase:** 1 Phase  
**Number of Receptacles:** 2  
**Receptacle Configuration:** Two NEMA 5-20 Ground Fault Receptacles  
**Control:** Two Single Pole 20 Ampere Breakers, No Main Breaker  
**Material:** G90 Galvanized Steel with Powder Coat Finish  
**Mounting:** Surface Mount  
**Cable Size:** 6 AWG to 2/0 AWG  
**Enclosure:** Type 3R



*Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.*

FEATURE TABLE		
ITEM	QTY	DESCRIPTION
A	4	U/L MNTG.EMBOSS
B	2	¼ SOLID K.O.
C	2	½, ¾, 1, 1¼, 1½ CONC. K.O.
D	1	¾, 1, 1¼, 1½, 2 CONC. K.O.
E	2	¼, ½, ¾, 1, 1¼, CONC. K.O.



Version:

1

All dimensions are +/- 1/16".  
 Drawing views are not to scale.  
 Utility requirements for this equipment may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.