



Catalog Number: U4908-O-11GR
Item Description: 100A RL MTR P/O
UPC Code: 784572271951

Brand Name: Milbank

Type: Ringless Metered Power Supply Unit

Special Features: 4 Terminal, Plain Top, Ground Bar, No Bypass, Single Power Head, 6 Branch Circuits

Application: Temporary Power

Standard: UL Listed

Voltage Rating: Up to 240 Volts Alternating Current

Amperage Rating: 125 Ampere Continuous

Wattage: Not Applicable

Frequency Rating: 60 Hertz

Phase: 1 Phase

Number of Receptacles: 2

Receptacle Configuration: Two NEMA 5-20 Ground Fault Receptacles

Control: Two Single Pole 20 Ampere Breakers, No Main Breaker

Material: G90 Galvanized Steel with Powder Coat Finish

Mounting: Surface Mount





Cable Size: 6 AWG to 2/0 AWG

Enclosure: Type 3R



Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.

| FEATURE TABLE | | |
|---------------|-----|----------------------------|
| ITEM | QTY | DESCRIPTION |
| A | 4 | U/L MNTG.EMBOSS |
| B | 2 | ¼ SOLID K.O. |
| C | 2 | ½, ¾, 1, 1¼, 1½ CONC. K.O. |
| D | 1 | ¾, 1, 1¼, 1½, 2 CONC. K.O. |
| E | 2 | ¼, ½, ¾, 1, 1¼, CONC. K.O. |



Version:

1

All dimensions are +/- 1/16".
Drawing views are not to scale.
Utility requirements for this equipment may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.



Catalog Number: U4908-O-11GR
Item Description: 100A RL MTR P/O
UPC Code: 784572271951

Brand Name: Milbank

Type: Ringless Metered Power Supply Unit

Special Features: 4 Terminal, Plain Top, Ground Bar, No Bypass, Single Power Head, 6 Branch Circuits

Application: Temporary Power

Standard: UL Listed

Voltage Rating: Up to 240 Volts Alternating Current

Amperage Rating: 125 Ampere Continuous

Wattage: Not Applicable

Frequency Rating: 60 Hertz

Phase: 1 Phase

Number of Receptacles: 2

Receptacle Configuration: Two NEMA 5-20 Ground Fault Receptacles

Control: Two Single Pole 20 Ampere Breakers, No Main Breaker

Material: G90 Galvanized Steel with Powder Coat Finish

Mounting: Surface Mount





Cable Size: 6 AWG to 2/0 AWG

Enclosure: Type 3R



Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.

| FEATURE TABLE | | |
|---------------|-----|----------------------------|
| ITEM | QTY | DESCRIPTION |
| A | 4 | U/L MNTG.EMBOSS |
| B | 2 | ¼ SOLID K.O. |
| C | 2 | ½, ¾, 1, 1¼, 1½ CONC. K.O. |
| D | 1 | ¾, 1, 1¼, 1½, 2 CONC. K.O. |
| E | 2 | ¼, ½, ¾, 1, 1¼, CONC. K.O. |



Version:

1

All dimensions are +/- 1/16".
Drawing views are not to scale.
Utility requirements for this equipment may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.