



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## V48M28T45EE 45KVA 3PH 480V TP-1 Delta Transformer

Eaton Corp

Catalog Number	V48M28T45EE
Manufacturer	Eaton Corp
Description	Eaton General Purpose Ventilated Transformer, DT-3 (3-Phase), PV 480V, Taps: 2 At +2.5% /4 At -2.5%, SV 208Y/120V, 150°C Rise W/ 200°C Insulation System, 45 Kva, Ee
Weight per unit	310.0 (lbs/each)
Product Category	Three Phase Energy Efficient D

### Features

dimensions	16.5000 IN X 23.0000 IN X 32.0200 IN
Number of Phases	Three-phase
Primary Voltage	480 V
Secondary Voltage	208 Y/120 V
Tap Size	2 at +2.5% FCAN, 4 at -2.5% FCBN

### Descriptions

Description	45KVA 3PH 480V TP-1 DELTA TRANSFORMER
extra long description	ETN V48M28T45EE 45KVA DT-3 TX 3PH 4
Features	Eaton types DS-3 (single-phase) and DT-3 (three-phase) general purpose ventilated dry-type transformers are two-winding, self-cooled, and available in a wide variety of primary and secondary voltage combinations. General purpose transformers are designed for continuous operation at rated kVA. They are designed, manufactured and tested in accordance with all of the latest applicable ANSI, NEMA and IEEE standards.
Long Description	Eaton General purpose ventilated transformer, DT-3 (3-phase), PV 480V, Taps: 2 at +2.5% /4 at -2.5%, SV 208Y/120V, 150°C rise w/ 200°C insulation system, 45 kVA, EE
Product Type	45KVA DT-3 TX 3PH 480D-208Y/120V 150C

### Manufacturer Information

Brand	Eaton
GTIN	00786680019357
Manufacturers Part Number	V48M28T45EE
UPC	786680019357

### Taxonomies, Classifications, and Categories

Category Description	3 PHASE TRANSFORMERS
Type	Ventilated transformer



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	310

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Safety and Security Systems
Frequency Rating	60 Hz
standard	UL Listed, NEMA TP-1 Compliant
Temperature Rating	150 °C rise