



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## SVX020A14A1B2 SVX9000 20HP 480V NEMA1 W/BR Chop Alfa PNL W/Conf *Eaton Corp*

Catalog Number	SVX020A14A1B2
Manufacturer	Eaton Corp
Description	Eaton SVX Adjustable Frequency Drive, 20HP, Nema Type 1/IP21, 480V, FR6, 3-Phase, Emc H, Standard Software, A/N Keypad, Int Brake Chopper, Varnished Boards
Weight per unit	46.3 (lbs/each)
Product Category	Ac Drives

### Features

dimensions	9.3000 IN X 7.6000 IN X 22.0000 IN
keypad	Alphanumeric

### Descriptions

Description	SVX9000 20HP 480V NEMA1 W/BR CHOP ALFA PNL W/CONF
extra long description	ETN SVX020A1-4A1B2 SVX9000 20HP 480
Features	Demand more accurate speed control. Eaton's SVX series of variable frequency drives offer sensorless vector control technology coupled with an adaptive motor model and sophisticated ASIC circuit features. This technology allows for steady speed error, fast torque rise time, high immunity to resonance vibrations and high starting torque and current. The SVX9000 is suitable for multiple motor drive systems and high-speed applications.
Long Description	Eaton SVX adjustable frequency drive, 20HP, NEMA Type 1/IP21, 480V, FR6, 3-phase, EMC H, Standard Software, A/N keypad, Int brake chopper, Varnished Boards
Product Type	SVX9000 20HP 480V N1 BC Alfa W/Conf Coat

### Manufacturer Information

Brand	Eaton
GTIN	00782116103874
Manufacturers Part Number	SVX020A14A1B2
UPC	782116103874

### Taxonomies, Classifications, and Categories

Category Description	DRIVES
Type	Adjustable frequency drive

### Availability

Status	Inactive
--------	----------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	46.2999

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
standard	UL 508C, IEC 61800-2, EN 61800-3 Level H, Contact Manufacturer