



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1200 Water St
78028-0000, TX Kerrville
Phone: 830-896-9240
Fax: 830-896-9244



VP10487 100 Amp Pin & Sleeve Plug 3-W 4-P 250 VDC/600 Vac

Hubbell-Killark

Catalog Number	VP10487
Manufacturer	Hubbell-Killark
Description	100A 3 Pole 4 Wire Plug Assembly
Weight per unit	4.0 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

Features

amperage rating	100
Cord Type	G, W, S, SO, STO, or similar
Material	Body-Copper-free aluminum;Contacts-Brass;External screws-316 stainless steel;Spring tensioner-Patented beryllium copper
Number of Wires	3
Phase	3
Poles	4
Voltage Rating	250:600
Wire Size	4-2

Dimensions and Weight

Size	10.87 in x 4.25 in x 4.25 in
------	------------------------------

Descriptions

Description	100 AMP PIN & SLEEVE PLUG 3-W 4-P 250 VDC/600 VAC
extra long description	KLRK VP10487 100A 3W4P PLUG ASSY.
Long Description	100A 3 Pole 4 Wire Plug Assembly
Product Type	100A 3W4P Plug Assy.
Special Features	VersaMate® metallic pin & sleeve plugs, receptacles, and in-line connectors are designed for heavy duty industrial use. These devices supply power to both fixed and portable electrical equipment including pumps, generators, welders, vacuums, blowers and similar apparatus. Suitable for indoor and outdoor use, as well as applications that include wet, cold, hosedown, hazardous and corrosive environments. Configurations are also available in reverse-service and polarized orientations.

Manufacturer Information

Brand	KILLARK
GTIN	00783936834764
Manufacturers Part Number	VP10487
series	VersaMate
UPC	783936834764



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1200 Water St
78028-0000, TX Kerrville
Phone: 830-896-9240
Fax: 830-896-9244

Taxonomies, Classifications, and Categories

Category Description	Pin & Sleeve Devices
Type	Pin & Sleeve

Packaging

Carton	1
Weight Per each	4

Uses, Certifications, and Standards

Application	Suitable for indoor or outdoor use. Applications include the wet, cold, hosedown, hazardous or corrosive areas in such industrial applications as:Pulp & Paper Mills, Electrical Power Plants, Petrochemical Plants, Wastewater Treatment, Marine, Docks, Ports, Construction Sites, Breweries, Re?neries, Chemical Plants, Grain Facilities , Textile Manufacturing, Food Processing Facilities
environmental conditions	Wet and hazardous locations
nema rating	NEMA 3, 4, 4X, 7BCD, 9FG
standard	UL, CSA