

# Eaton SVX125A1-4A1N1

Catalog Number: SVX125A1-4A1N1

Eaton SVX adjustable frequency drive, 125HP, NEMA Type 1/IP21, 480V, FR8, Three-phase, EMC H, Standard Software, A/N keypad, No brake chopper, Standard boards



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton SVX adjustable frequency drive	SVX125A1-4A1N1
<b>UPC</b>	<b>Product Length/Depth</b>
782116011599	13.5 in
<b>Product Height</b>	<b>Product Width</b>
30.1 in	11.5 in
<b>Product Weight</b>	<b>Warranty</b>
127 lb	2 year
<b>Compliances</b>	<b>Certifications</b>
Contact Manufacturer	IEC 61800-2
	UL 508C
	EN 61800-3 Level H

## defaultTaxonomyAttributeLabel

[Brake chopper](#)

No brake chopper

[Modification](#)

Standard boards

[Horsepower](#)

125 hp

[Frame size](#)

8

[Keypad](#)

Alphanumeric

[Input](#)

EMC H

Three-phase

[Rating](#)

NEMA 1, IP21

[Software](#)

Standard

## Resources

[Application notes](#)

SPI - Variable frequency drives with a common DC bus

Electromagnetic compatibility (EMC)

Connecting drives to generator supplies

[Brochures](#)

SVX9000 Adjustable Frequency Drives Brochure

SVX9000 Adjustable Frequency Drives Product Aid

[Catalogs](#)

Product Range Catalog Drives Engineering

Eaton's Volume 6—Solid-State Motor Control

Product Datasheet - SVX125A1-4A1N1

[Drawings](#)

SVX\_(FR8) 3D Inventor

SVX\_(FR8) AutoCAD 2D Footprint

SVX\_(FR8) 2D Drawing Xchange

SVX\_(FR8) AutoCAD 2D Footprint (mm)

SVX\_(FR8) 2D PDF

SVX\_(FR8) 3D Model Xchange

SVX and SPX Series FR4-FR11 PDF Open Drawings

[Installation instructions](#)

9000X AFD User Manual

[Specifications and datasheets](#)

Eaton Specification Sheet - SVX125A1-4A1N1



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia