

Eaton T20P11S5016

Catalog Number: T20P11S5016

Eaton General purpose ventilated transformer, NEMA 2, FR843A, 60 Hz, 50 kVA, Single-phase, 240X480V, 120/240 V, NEMA ST-20, 1 at +5%, 2 at -5% x 2 at +2.5%, 4 at -2.5%, 50 kVA, 240 X 480 Vac-120/240 V, 3XA, DOE 2016



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	T20P11S5016
	UPC
	786680147647

Product Length/Depth	Product Height
24.38 in	38.7 in

Product Width	Product Weight
23.51 in	408 lb

Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year DOE2016 Efficient from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications
	UL Listed
	OSHPD Certified

Catalog Notes
10 CFR Part 431 (2016) Efficient

Physical Attributes

Coil material

Aluminum

Enclosure

NEMA 2

Frame

FR843A

Insulation

220 °C

Mounting

Floor or wall, upright only

Tap size

1 at +5%, 2 at -5% x 2 at +2.5%, 4 at -2.5%

Type

Energy-efficient ventilated type DS-3 transformer

Wiring connection

3XA

Performance Ratings

Efficiency

10 CFR Part 431-2016 (DOE 2016)

Frequency rating

60 Hz

Kva Rating

50 kVA

Primary voltage

240 V, 480 V

Secondary Voltage

120/240 V

Sound Level

NEMA ST-20

Temperature rise

150 °C rise

Volt ampere rating

50 kVA

Miscellaneous

Weathershield

WS43A

Resources

Brochures

[Eaton's high-efficiency dry-type transformers](#)

[Eaton's low-voltage dry-type distribution transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - T20P11S5016](#)