

# Specifications



## Eaton XBUT35

Eaton XB IEC terminal block, 16 mm Screw connection single level-through-feed, Gray, 8 AWG/6 mm<sup>2</sup> maximum wire, IEC 800V, EN 700V, UL 600V, IEC #24-8 AWG, EN #24-8 AWG, UL #24-8 AWG wire, IEC 57A, EN 40,50A, UL 50A

### General specifications

<b>PRODUCT NAME</b>	Eaton XB IEC terminal block
<b>CATALOG NUMBER</b>	XBUT35
<b>UPC</b>	782116905065
<b>PRODUCT LENGTH/DEPTH</b>	2.37 in
<b>PRODUCT HEIGHT</b>	2.88 in
<b>PRODUCT WIDTH</b>	0.63 in
<b>PRODUCT WEIGHT</b>	0.02 lb
<b>WARRANTY</b>	1 year
<b>CERTIFICATIONS</b>	CSA Certified UL Listed



*Powering Business Worldwide*

### Product specifications

<b>TYPE</b>	IEC-XB Series
<b>AMPERAGE RATING</b>	527 (IEC), 40A (EN), 50A (EN), 50A (UL)
<b>VOLTAGE RATING</b>	IEC 800V, EN 700V, UL 600V

### Resources

<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - XBUT35</a>
--------------------------------------	--

---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

---



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications



## Eaton XBUT35

Eaton XB IEC terminal block, 16 mm Screw connection single level-through-feed, Gray, 8 AWG/6 mm<sup>2</sup> maximum wire, IEC 800V, EN 700V, UL 600V, IEC #24-8 AWG, EN #24-8 AWG, UL #24-8 AWG wire, IEC 57A, EN 40,50A, UL 50A

### General specifications

<b>PRODUCT NAME</b>	Eaton XB IEC terminal block
<b>CATALOG NUMBER</b>	XBUT35
<b>UPC</b>	782116905065
<b>PRODUCT LENGTH/DEPTH</b>	2.37 in
<b>PRODUCT HEIGHT</b>	2.88 in
<b>PRODUCT WIDTH</b>	0.63 in
<b>PRODUCT WEIGHT</b>	0.02 lb
<b>WARRANTY</b>	1 year
<b>CERTIFICATIONS</b>	CSA Certified UL Listed



*Powering Business Worldwide*

### Product specifications

<b>TYPE</b>	IEC-XB Series
<b>AMPERAGE RATING</b>	527 (IEC), 40A (EN), 50A (EN), 50A (UL)
<b>VOLTAGE RATING</b>	IEC 800V, EN 700V, UL 600V

### Resources

<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - XBUT35</a>
--------------------------------------	--

---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

---



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

