

Eaton XJG64 HDG

Catalog Number: XJG64 HDG

Eaton Crouse-Hinds series XJG expansion coupling, Rigid/IMC, Steel, Hot dip galvanized finish, 4" maximum conduit movement, 2" trade size

Photo is representative

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series XJG expansion coupling	XJG64 HDG
	UPC
	662276271517
Product Length/Depth	Product Height
8.75 in	4.38 in
Product Width	Product Weight
4.38 in	8.9 lb



Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Type

Expansion

Conduit type

Rigid/IMC

Trade size

2"

Conduit movement - max

4"

Material

Steel

Finish

Hot dip galvanized

Resources

Brochures

[Crouse-Hinds series Conduit Expansion/Deflection Couplings brochure](#)

[Crouse-Hinds series Hot Dip Galvanized Products brochure](#)

Catalogs

[Crouse-Hinds series XJG Conduit Expansion Couplings for Rigid/IMC catalog page](#)

Certification reports

[XJG Conduit Expansion Couplings for EMT and Rigid/IMC UL certification](#)

[XJG Conduit Expansion Couplings for EMT and Rigid/IMC Canadian certification](#)

Installation instructions

[IF 1508 - Assembly-Free XJG](#)

[IF 343 - Type XJ Expansion Joints](#)

Specifications and datasheets

[Expansion and Deflection Couplings](#)

[Eaton Specification Sheet - XJG64 HDG](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton XJG64 HDG

Catalog Number: XJG64 HDG

Eaton Crouse-Hinds series XJG expansion coupling, Rigid/IMC, Steel, Hot dip galvanized finish, 4" maximum conduit movement, 2" trade size

Photo is representative

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series XJG expansion coupling	XJG64 HDG
	UPC
	662276271517
Product Length/Depth	Product Height
8.75 in	4.38 in
Product Width	Product Weight
4.38 in	8.9 lb



Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Type

Expansion

Conduit type

Rigid/IMC

Trade size

2"

Conduit movement - max

4"

Material

Steel

Finish

Hot dip galvanized

Resources

Brochures

[Crouse-Hinds series Conduit Expansion/Deflection Couplings brochure](#)

[Crouse-Hinds series Hot Dip Galvanized Products brochure](#)

Catalogs

[Crouse-Hinds series XJG Conduit Expansion Couplings for Rigid/IMC catalog page](#)

Certification reports

[XJG Conduit Expansion Couplings for EMT and Rigid/IMC UL certification](#)

[XJG Conduit Expansion Couplings for EMT and Rigid/IMC Canadian certification](#)

Installation instructions

[IF 1508 - Assembly-Free XJG](#)

[IF 343 - Type XJ Expansion Joints](#)

Specifications and datasheets

[Expansion and Deflection Couplings](#)

[Eaton Specification Sheet - XJG64 HDG](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)