



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TM826USBW 3.1 Usb + Duplex 15A WH

Pass & Seymour/Legrand

| | |
|------------------|--|
| Catalog Number | TM826USBW |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Usb + Duplex Outlet, White, 125 V, 15 A, Nylon (Back Body); Polycarbonate (Face) Material, #14 to #10 Awg Wire Size, -40 °C Operating Temperature, +60 °C Operating Temperature, 1.693 In Length, 1.35 In Width, 4.18 In Height, 0.3100 LB |
| Weight per unit | 0.3050 (lbs/each) |
| Product Category | Wiring Devices |

Features

| | |
|---------------------|--------------------------------|
| Dielectric Strength | Withstands 1500V minimum |
| indoor/outdoor | Indoor |
| media | Yes |
| Mounting Type | Box |
| Number of Gangs | 1.0 |
| Outlet Type | USB-Charging, Tamper-Resistant |
| Poles | Double Pole |
| Voltage | 125.0 V |

Material, Color, and Finish

| | |
|--------|-------|
| Finish | Matte |
|--------|-------|

Descriptions

| | |
|------------------------|------------------------------------|
| Description | 3.1 USB + DUPLEX 15A WH |
| extra long description | P&S TM826USBW 3.1 USB + DUPLEX 15A |

Manufacturer Information

| | |
|-------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007127652 |
| UPC | 785007127652 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------------|
| Category Description | Residential receptacles |
| Type | Outlet |

Trade Size

| | |
|----------|------|
| Amperage | 15.0 |
|----------|------|

Packaging

| | |
|-----------------|-------|
| Carton | 10 |
| Package | 50 |
| Weight Per each | 0.305 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| environmental conditions | 95% (relative humidity, non-condensing) |
| nema rating | 15A |
| standard | UL, CSA, CSA, CULUS, ROHS, ROHS, UL, UL94 V2 (for device cover) |
| | 5V (for device body and frame), RoHS |