



**Dependable, high-performance solutions brought to you by Legrand.**

TM870, TM873, TM874

Now part of the radiant® collection, our paddle switches offer a better fit, form and finish. The smooth paddle action combines with subtle aesthetic improvements to deliver reliable performance. ON-OFF switches conform to NEMA 430-104 requirements for kitchen disposal units. Ideal for residential, multi-dwelling, commercial office and hospitality applications.

## Features & Benefits

**Easy-access green hex head ground screw.**

**External screw-pressure-plate back and side wired.** Accepts #12 and #14 AWG.

**Extra-long, through-body strap** eliminates floating installations and imperfect applications.

**High-impact resistant thermoplastic construction.**



**TM870LA**

- Part of the radiant® collection.
- Smooth paddle action.
- Push wire #14 AWG.
- Narrow back body leaves more room for wires in the box.

- Tri-drive ground, terminal and mounting screws.
- ON-OFF switches conform to NEC 430-104 requirements for kitchen disposal units.
- NAFTA-Compliant Switches are ideal for use on projects subject to the provisions of the Buy American Act.

## Compliance



cULus Listed, UL20, Conform to NEMA WD-1 and WD-6 UL Listed, File Number E140596, Standard UL20. cULus listed. Standard CSA C22.2 No. 111. Conform to NEMA WD-1 and WD-6.

## Technical Information

### Performance

#### Electrical

Maximum Working Voltage	277VAC
Maximum Current Interrupting	15A
Maximum Temperature Rise	30°C

#### Mechanical


Terminal Identification	Terminal identification in accordance with UL20
Terminal Accommodation	Back and side wire terminals accommodate #12 and #14 AWG stranded and copper wire Push wire terminals accommodate #14 AWG
Product Identification	Ratings are a permanent part of the device

#### Environmental

Flammability	UL20 minimum rating
--------------	---------------------

### Materials

Face	Thermoplastic
Back Body	Thermoplastic
Line Contacts	.031 Brass
Mounting Strap	.042 Zinc-Plated Steel
Tamper-Resistant Shutters	Thermoplastic
Terminal Screws	#8 Tri-Drive Steel (Neutral = Nickel-Plated Steel)
Ground Screw	#8 Hex Tri-Drive Steel; Zinc Coating with Green Chromate
Mounting Screws	Steel plated





**TM873 LA**

## Warranty

1 Year

## Ordering Information

### Single Pole Switches Grounding

Catalog Number	Rating		Color	3rd Party Compliance	
	A	VAC		 UL20	 C22.2 111
TM870I	15	120/277	Ivory	•	•
TM870W	15	120/277	White	•	•
TM870	15	120/277	Brown	•	•
TM870GRY	15	120/277	Gray	•	•
TM870BK	15	120/277	Black	•	•
TM870LA	15	120/277	Light Almond	•	•
TM870NICC10	15	120/277	Nickel	•	•
TM870DBCC10	15	120/277	Dark Bronze	•	•

### Three-Way Switches Grounding

TM873I	15	120/277	Ivory	•	•
TM873W	15	120/277	White	•	•
TM873	15	120/277	Brown	•	•
TM873GRY	15	120/277	Gray	•	•
TM873BK	15	120/277	Black	•	•
TM873LA	15	120/277	Light Almond	•	•
TM873NICC10	15	120/277	Nickel	•	•
TM873DBCC10	15	120/277	Dark Bronze	•	•

### Four-Way Switches Grounding

TM874I	15	120/277	Ivory	•	•
TM874W	15	120/277	White	•	•
TM874	15	120/277	Brown	•	•
TM874BK	15	120/277	Black	•	•
TM874LA	15	120/277	Light Almond	•	•
TM874NICC6	15	120/277	Nickel	•	•
TM874DBCC6	15	120/277	Dark Bronze	•	•

---

## Vertical Markets


- Office
- Residential
- Multiple Dwelling
- Hospitality/Lodging

---

## Also available in the radiant® collection

- GFCI Receptacles
- Standard & Tamper-Resistant Receptacles
- Lighting & Fan Controls
- Timers
- Combination Devices
- USB Charging Devices
- Night Lights
- Screwless Wall Plates
- Sensors
- Home Automation Controls

---

 The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act compliant. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.



**Legrand, North America**  
60 Woodlawn Street  
West Hartford, CT 06110  
1.877.BY.LEGRAND (295.3472)  
[www.legrand.us](http://www.legrand.us)

570 Applewood Crescent  
Vaughan, Ontario L4K 4B4  
905.738.9195  
[www.legrand.ca](http://www.legrand.ca)

FOLLOW US





**Dependable, high-performance solutions brought to you by Legrand.**

TM870, TM873, TM874

Now part of the radiant® collection, our paddle switches offer a better fit, form and finish. The smooth paddle action combines with subtle aesthetic improvements to deliver reliable performance. ON-OFF switches conform to NEMA 430-104 requirements for kitchen disposal units. Ideal for residential, multi-dwelling, commercial office and hospitality applications.


## Features & Benefits

**Easy-access green hex head ground screw.**

**External screw-pressure-plate back and side wired.** Accepts #12 and #14 AWG.

**Extra-long, through-body strap** eliminates floating installations and imperfect applications.

**High-impact resistant thermoplastic construction.**



**TM870LA**

- Part of the radiant® collection.
- Smooth paddle action.
- Push wire #14 AWG.
- Narrow back body leaves more room for wires in the box.

- Tri-drive ground, terminal and mounting screws.
- ON-OFF switches conform to NEC 430-104 requirements for kitchen disposal units.
- NAFTA-Compliant Switches are ideal for use on projects subject to the provisions of the Buy American Act.

## Compliance



cULus Listed, UL20, Conform to NEMA WD-1 and WD-6 UL Listed, File Number E140596, Standard UL20. cULus listed. Standard CSA C22.2 No. 111. Conform to NEMA WD-1 and WD-6.

## Technical Information

### Performance

#### Electrical

Maximum Working Voltage	277VAC
Maximum Current Interrupting	15A
Maximum Temperature Rise	30°C

#### Mechanical


Terminal Identification	Terminal identification in accordance with UL20
Terminal Accommodation	Back and side wire terminals accommodate #12 and #14 AWG stranded and copper wire Push wire terminals accommodate #14 AWG
Product Identification	Ratings are a permanent part of the device

#### Environmental

Flammability	UL20 minimum rating
--------------	---------------------

### Materials

Face	Thermoplastic
Back Body	Thermoplastic
Line Contacts	.031 Brass
Mounting Strap	.042 Zinc-Plated Steel
Tamper-Resistant Shutters	Thermoplastic
Terminal Screws	#8 Tri-Drive Steel (Neutral = Nickel-Plated Steel)
Ground Screw	#8 Hex Tri-Drive Steel; Zinc Coating with Green Chromate
Mounting Screws	Steel plated





**TM873 LA**

## Warranty

1 Year

## Ordering Information

### Single Pole Switches Grounding

Catalog Number	Rating		Color	3rd Party Compliance	
	A	VAC		 UL20	 C22.2 111
TM870I	15	120/277	Ivory	•	•
TM870W	15	120/277	White	•	•
TM870	15	120/277	Brown	•	•
TM870GRY	15	120/277	Gray	•	•
TM870BK	15	120/277	Black	•	•
TM870LA	15	120/277	Light Almond	•	•
TM870NICC10	15	120/277	Nickel	•	•
TM870DBCC10	15	120/277	Dark Bronze	•	•

### Three-Way Switches Grounding

TM873I	15	120/277	Ivory	•	•
TM873W	15	120/277	White	•	•
TM873	15	120/277	Brown	•	•
TM873GRY	15	120/277	Gray	•	•
TM873BK	15	120/277	Black	•	•
TM873LA	15	120/277	Light Almond	•	•
TM873NICC10	15	120/277	Nickel	•	•
TM873DBCC10	15	120/277	Dark Bronze	•	•

### Four-Way Switches Grounding

TM874I	15	120/277	Ivory	•	•
TM874W	15	120/277	White	•	•
TM874	15	120/277	Brown	•	•
TM874BK	15	120/277	Black	•	•
TM874LA	15	120/277	Light Almond	•	•
TM874NICC6	15	120/277	Nickel	•	•
TM874DBCC6	15	120/277	Dark Bronze	•	•

---

## Vertical Markets


- Office
- Residential
- Multiple Dwelling
- Hospitality/Lodging

---

## Also available in the radiant® collection

- GFCI Receptacles
- Standard & Tamper-Resistant Receptacles
- Lighting & Fan Controls
- Timers
- Combination Devices
- USB Charging Devices
- Night Lights
- Screwless Wall Plates
- Sensors
- Home Automation Controls

---

 The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act compliant. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.



**Legrand, North America**  
60 Woodlawn Street  
West Hartford, CT 06110  
1.877.BY.LEGRAND (295.3472)  
[www.legrand.us](http://www.legrand.us)

570 Applewood Crescent  
Vaughan, Ontario L4K 4B4  
905.738.9195  
[www.legrand.ca](http://www.legrand.ca)

FOLLOW US

