

# Eaton XTCR080F11A

Catalog Number: XTCR080F11A

Eaton XT IEC contactor, 80A, Top-mounted, 110 Vac 50 Hz, 120 Vac 60 Hz, 1NO-1NC, 80A, Frame F, 90 mm, 50-60 Hz, 7.5, 15/25, 30, 60, 75 hp (1/3PH @ 115, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVR



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton XT IEC contactor	XTCR080F11A
<b>UPC</b>	<b>Product Length/Depth</b>
782116356126	9.5 in
<b>Product Height</b>	<b>Product Width</b>
6 in	6.5 in
<b>Product Weight</b>	<b>Compliances</b>
4.7 lb	CE Marked RoHS Compliant
<b>Certifications</b>	<b>Catalog Notes</b>
UL Listed CSA Certified IEC 60947 EN 60947	Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

## defaultTaxonomyAttributeLabel

### Amperage Rating

80A

### HP rating - max

7.5, 15/ 25, 30, 60, 75 hp (1/3PH @115,230/200,230,460,575 V)

### Number Of Poles

Three-pole

### Type

Full voltage reversing contactor

### Frequency rating

50-60 Hz

### Terminals

Screw terminals

### Coil voltage

110-120 Vac, 50/60 Hz

### Contact configuration

1 NO, 1 NC

### Continuous ampere rating

80 A

### Series

XT IEC

### Operation

Reversing

## Resources

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Drawings

[XTCR\\_F 2D Drawing Xchange](#)

[XTCR\\_F AutoCAD 2D Footprint](#)

[XTCR\\_F 3D Model Xchange](#)

[XTCR\\_F 2D PDF](#)

[XTCR\\_F 3D Inventor](#)

[XTCR\\_F AutoCAD 2D Footprint \(mm\)](#)

### Specifications and datasheets

[Eaton Specification Sheet - XTCR080F11A](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)