



MILBANK
ENERGY AT WORK

U4908-O-11GR







| | |
|-------------------------------|--|
| Catalog Number | U4908-O-11GR |
| Marketing Product Description | 4 Terminal Ringless Plain Top 520GR 520GR Surface Mount |
| UPC | 784572271951 |
| Length (IN) | 5.188 |
| Width (IN) | 9 |
| Height (IN) | 25.938 |
| Brand Name | Milbank |
| Type | Ringless Meter Socket |
| Special Features | Two Single Pole 20 Ampere Breakers |
| Application | Temporary Power |
| Standard | UL Listed;Type 3R |
| Voltage Rating | Up to 240 Volts Alternating Current |
| Amperage Rating | 125 Continuous Ampere |
| Phase | 1 Phase |
| Frequency Rating | 60 Hertz |
| Size | 5.188L x 9W x 25.938H |
| Number Of Cutouts | 2 |
| Cutout Size | Two Single Pole 20 Ampere Breakers |
| Cable Entry | Underground |
| Terminal | Lay in |

| | |
|---------------------------|---|
| Insulation | Glass Polyester |
| Mounting | Surface Mount |
| Enclosure | G90 Galvanized Steel with Powder Coat Finish |
| Jaw Quantity | 4 Terminal |
| Bypass Type | No Bypass |
| Number of Meter Positions | Single Power Head |
| Equipment Ground | Ground Bar |
| Hub Opening | Plain Top |
| Number Branch Circuits | 4 |
| Number Of Receptacles | 2 |
| Receptacle Configuration | Two NEMA 5-20 Ground Fault |

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.

| FEATURE TABLE | | |
|---------------|-----|----------------------------|
| ITEM | QTY | DESCRIPTION |
| A | 4 | U/L MNTG.EMBOSS |
| B | 2 | ¼ SOLID K.O. |
| C | 2 | ½, ¾, 1, 1¼, 1½ CONC. K.O. |
| D | 1 | ¾, 1, 1¼, 1½, 2 CONC. K.O. |
| E | 2 | ¼, ½, ¾, 1, 1¼, CONC. K.O. |



Version:

1

**All dimensions are +/- 1/16".
Drawing views are not to scale.**

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility, and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.



MILBANK
ENERGY AT WORK

U4908-O-11GR







| | |
|-------------------------------|--|
| Catalog Number | U4908-O-11GR |
| Marketing Product Description | 4 Terminal Ringless Plain Top 520GR 520GR Surface Mount |
| UPC | 784572271951 |
| Length (IN) | 5.188 |
| Width (IN) | 9 |
| Height (IN) | 25.938 |
| Brand Name | Milbank |
| Type | Ringless Meter Socket |
| Special Features | Two Single Pole 20 Ampere Breakers |
| Application | Temporary Power |
| Standard | UL Listed;Type 3R |
| Voltage Rating | Up to 240 Volts Alternating Current |
| Amperage Rating | 125 Continuous Ampere |
| Phase | 1 Phase |
| Frequency Rating | 60 Hertz |
| Size | 5.188L x 9W x 25.938H |
| Number Of Cutouts | 2 |
| Cutout Size | Two Single Pole 20 Ampere Breakers |
| Cable Entry | Underground |
| Terminal | Lay in |

| | |
|---------------------------|---|
| Insulation | Glass Polyester |
| Mounting | Surface Mount |
| Enclosure | G90 Galvanized Steel with Powder Coat Finish |
| Jaw Quantity | 4 Terminal |
| Bypass Type | No Bypass |
| Number of Meter Positions | Single Power Head |
| Equipment Ground | Ground Bar |
| Hub Opening | Plain Top |
| Number Branch Circuits | 4 |
| Number Of Receptacles | 2 |
| Receptacle Configuration | Two NEMA 5-20 Ground Fault |

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.

| FEATURE TABLE | | |
|---------------|-----|----------------------------|
| ITEM | QTY | DESCRIPTION |
| A | 4 | U/L MNTG.EMBOSS |
| B | 2 | ¼ SOLID K.O. |
| C | 2 | ½, ¾, 1, 1¼, 1½ CONC. K.O. |
| D | 1 | ¾, 1, 1¼, 1½, 2 CONC. K.O. |
| E | 2 | ¼, ½, ¾, 1, 1¼, CONC. K.O. |



Version:

1

**All dimensions are +/- 1/16".
Drawing views are not to scale.**

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility, and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.