



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



YGHP29C2 #2SOL TP #2SOL 32/17ST Burndy LLC

| | |
|------------------|--|
| Catalog Number | YGHP29C2 |
| Manufacturer | Burndy LLC |
| Description | Cu Compression Ground Rod Connector, #4 Sol - #2 STR, 1/2" - 5/8" Rod Dia. |
| Weight per unit | 0.2700 (lbs/each) |
| Product Category | Large Terminals & Connectors |

Features

| | |
|-----------------|--------|
| Die Index | 997 |
| Material | Copper |
| pallet quantity | 7350 |

Descriptions

| | |
|------------------------|--|
| Description | #2SOL TP #2SOL 32/17ST |
| extra long description | BUR YGHP29C2 1/0-250 TO 4 SOL-2 STR |
| Long Description | Cu Compression Ground Rod Connector, #4 Sol - #2 Str, 1/2" - 5/8" Rod Dia. |
| Product Type | Compression |
| Special Features | Features: Irreversible Compression Ground Tap Can Be Used As A Tap Connector Or As A Tap Splice Connector, Four Die Sets And Eight Connectors Can Accommodate A Conductor Range From #8 AWG Solid Through 500 KCMIL Plus 1/2 IN, 5/8 IN, And 3/4 IN Copper Bonded Ground Rods, UL467 Listed, Acceptable For Direct Burial In Earth And Concrete, Prefilled With PENETROX Compound And Strip Sealed, Conductor Type: Run: Commercial Stranded Copper, Rebar, Ground Rod, Tap: Commercial Stranded Copper, Conductor Size (run - |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | BURNDY |
| GTIN | 00781810220924 |
| Manufacturers Part Number | YGHP29C2 |
| UPC | 781810220924 |

Taxonomies, Classifications, and Categories

| | |
|------|------|
| Type | Taps |
|------|------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 0.27 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------------|---|
| Application | For Direct Burial In Earth And Concrete |
| standard | Direct Burial |