Conductor Jacket			With Ground				Without Ground		Allowable	Standard	
Size (AWG)	No. Strands	Insulation and Jacket Thickness (mils)	Thickness - (mils)	Ground Wire		Cable Dimension	Approx. Net Weight	Cable Dimension	Approx. Net Weight	Ampacity+	Package
				Size (AWG)	No. Strands	(mils)	Per 1000' (Ibs.)	(mils)	Per 1000' (Ibs.)		l
					TWO COM	NDUCTOR					
14	1	19	30	14	1	423 X 168	70	354 X 168	52	15	EQ
12	1	19	30	12	1	463 X 183	95	386 X 183	70	20	EQ
10	1	24	30	10	1	518 X 215	138	440 X 215	102	30	EQ
8	7	35	45	10	1	678 X 302	222	576 X 302	178	40	СК
6	7	35	45	10	1	770 X 338	303	668 X 338	256	55	СК
	-				THREE CC	NDUCTOR					
14	1	19	30	14	1	581 X 168	96	501 X 168	77	15	EQ
12	1	19	30	12	1	626 X 183	129	581 X 183	108	20	BQ
10	1	24	30	10	1	727 X 215	191	661 X 215	156	30	BQ
8	7	35	45	10	1	1059 X 319	344	984 X 319	304	40	СК
6	7	35	45	10	1	1223 X 361	478	1153 X 361	437	55	СК
		Subject to spe ors in cable pe		, National Ele	ectrical Code, :	2008 Edition.				STANDARD P CODE -B 1000' Ree -C 500' Reel -E 1000' Spo -H 250' Spoo -K 125' Coil -P 500' Carto -Q 250' Carto	l ol l

#### **RECOMMENDED SAMPLE SPECIFICATIONS:**

Cable shall be UL-listed Type UF-B, suitable for operation at 600 volts or less in all installations as specified in the National Electrical Code. Conductors shall be annealed copper as manufactured by Southwire Company or approved equal.





Copyright 2003, Southwire Company. All Rights Reserved.

<sup>®</sup>Southwire is a registered trademark of Southwire Company.



#### Underground Feeder and Branch Circuit Cable. 600 Volt. Copper Conductors. Sunlight, Moisture, and Fungus Resistant Overall PVC Jacket.



# **APPLICATIONS**

Southwire Type UF-B cable is generally used as feeder to outside post lamps, pumps, and other loads or apparatus fed from a distribution point in an existing building as specified in the National Electrical Code<sup>1</sup>. UF-B cable may be used underground, including direct burial. Multiple conductor UF-B cable may be used for interior branch circuit wiring in residential or agricultural buildings at conductor temperatures not to exceed 90°C (with ampacity limited to that for 60°C conductors) as specified by the National Electrical Code. UF-B can be used in applications permitted for NMC in Section 334.10(B) of the National Electrical Code. Voltage rating for UF-B cable is 600 volts.

### **SPECIFICATIONS**

Southwire Type UF-B cable meets or exceeds UL Standard 83, UL Standard 493, Federal Specification A-A-59544, and requirements of the National Electrical Code.

# CONSTRUCTION

Southwire Type UF-B cable is manufactured as a 2 or 3 conductor cable, with or without a ground wire. Copper conductors are annealed (soft) copper, solid or compressed stranded. Phase conductors are polyvinyl chloride (PVC) insulated, nylon jacketed, color coded for identification purposes. Jacketed with sunlight, moisture and fungus resistant gray PVC.

<sup>1</sup> 2008 Edition.





Copyright 2003, Southwire Company. All Rights Reserved.