

Safety Data Sheet

Printing date 01/25/2016

Revised On 01/25/2016

1 Identification of the substance and manufacturer

Trade name: GLOSS WHITE
Product code: 0000100002
Product category: PC9a Paints and coatings.
Manufacturer/Supplier: Seymour of Sycamore
 917 Crosby Avenue
 Sycamore, IL 60178
 Phone: 815-895-9101 www.seymourpaint.com
Emergency telephone number: CHEMTEL 1-800-255-3924, or 813-248-0585.

2 Hazard(s) identification

Classification of the substance or mixture

Flam. Aerosol 1 H222 Extremely flammable aerosol.
 Press. Gas H280 Contains gas under pressure; may explode if heated.
 Skin Irrit. 2 H315 Causes skin irritation.
 Eye Irrit. 2A H319 Causes serious eye irritation.
 Repr. 2 H361 Suspected of damaging fertility or the unborn child.
 STOT SE 3 H336 May cause drowsiness or dizziness.
 STOT RE 2 H373 May cause damage to organs through prolonged or repeated exposure.

GHS Hazard pictograms



GHS02 GHS04 GHS07 GHS08

Signal word

Hazard statements

Danger
 Extremely flammable aerosol.
 Contains gas under pressure; may explode if heated.
 Causes skin irritation.
 Causes serious eye irritation.
 Suspected of damaging fertility or the unborn child.
 May cause drowsiness or dizziness.
 May cause damage to organs through prolonged or repeated exposure.
 Obtain special instructions before use.
 Keep away from heat/sparks/open flames/hot surfaces. No smoking.
 Do not spray on an open flame or other ignition source.
 Do not pierce or burn, even after use.
 Wash hands thoroughly after handling.
 Use only outdoors or in a well-ventilated area.
 Wear protective gloves/protective clothing/eye protection/face protection.
 Do not handle until all safety precautions have been read and understood.
 Wear protective gloves.
 Do not breathe dust/fume/gas/mist/vapors/spray.
 IF INHALED: Remove person to fresh air and keep comfortable for breathing.
 If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
 Call a POISON CENTER/doctor if you feel unwell.
 If skin irritation occurs: Get medical advice/attention.
 IF ON SKIN: Wash with plenty of water.
 If eye irritation persists: Get medical advice/attention.
 Take off contaminated clothing and wash it before reuse.
 Store locked up.
 Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.
 Protect from sunlight. Store in a well-ventilated place.
 Store in a well-ventilated place. Keep container tightly closed.
 Dispose of contents/container in accordance with local/regional/national/international regulations.

Precautionary statements

3 Composition/information on ingredients

Chemical characterization: Mixtures

Chemical Description:

This product is a mixture of the substances listed below with nonhazardous additions.

Dangerous components:

67-64-1	Acetone	24.35%
74-98-6	propane	22.04%
108-88-3	Toluene	21.4%
106-97-8	n-butane	12.94%
13463-67-7	titanium dioxide	5.42%
64742-89-8	VM&P Naphtha	3.57%
64742-47-8	Mineral Spirits	1.14%
1330-20-7	xylene (mix)	1.13%

4 First-aid measures

After inhalation:

Supply fresh air; consult doctor in case of complaints.

After skin contact:

Immediately wash with water and soap and rinse thoroughly.

After eye contact:

Remove contaminated clothing. Wash exposed area with soap and water.
Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.

After swallowing:

Rinse out mouth and then drink plenty of water.
Rinse mouth with water. Do not induce vomiting.

(Contd. on page 2)

Safety Data Sheet

Printing date 01/25/2016

Revised On 01/25/2016

Trade name: GLOSS WHITE

(Contd. of page 1)

Most important symptoms and effects:

Dizziness

Indication of any immediate medical attention needed:

No further relevant information available.

5 Fire-fighting measures**Extinguishing agents:**CO₂, extinguishing powder or water spray. Fight larger fires with water spray.**Special hazards:**

Can form explosive gas-air mixtures.

Protective equipment for firefighters:

A respiratory protective device may be necessary.

6 Accidental release measures**Personal precautions, protective equipment and emergency procedures:**Wear protective equipment. Keep unprotected persons away.
Use respiratory protective device against the effects of fumes/dust/aerosol.**Methods and material for containment and cleaning up:**Ensure adequate ventilation.
Dispose contaminated material as waste according to section 13.**7 Handling and storage****Precautions for safe handling**

Use only in well ventilated areas.

Storage requirements:

Keep away from sources of heat and direct sunlight. Do not warehouse in subfreezing conditions. Store locked up.

8 Exposure controls/personal protection**Components with limit values that require monitoring at the workplace:****67-64-1 Acetone**PEL (USA) Long-term value: 2400 mg/m³, 1000 ppmREL (USA) Long-term value: 590 mg/m³, 250 ppmTLV (USA) Short-term value: 1187 mg/m³, 500 ppmLong-term value: 594 mg/m³, 250 ppm

BEI

74-98-6 propanePEL (USA) Long-term value: 1800 mg/m³, 1000 ppmREL (USA) Long-term value: 1800 mg/m³, 1000 ppm

TLV (USA) refer to Appendix F in TLVs and BEIs book

108-88-3 ToluenePEL (USA) Long-term value: 200 ppm
Ceiling limit value: 300; 500* ppm
*10-min peak per 8-hr shiftREL (USA) Short-term value: 560 mg/m³, 150 ppmLong-term value: 375 mg/m³, 100 ppmTLV (USA) Long-term value: 75 mg/m³, 20 ppm

BEI

106-97-8 n-butaneREL (USA) Long-term value: 1900 mg/m³, 800 ppmTLV (USA) Short-term value: 2370 mg/m³, 1000 ppm**1330-20-7 xylene (mix)**PEL (USA) Long-term value: 435 mg/m³, 100 ppmREL (USA) Short-term value: 655 mg/m³, 150 ppmLong-term value: 435 mg/m³, 100 ppmTLV (USA) Short-term value: 651 mg/m³, 150 ppmLong-term value: 434 mg/m³, 100 ppm

BEI

Ingredients with biological limit values:**67-64-1 Acetone**

BEI (USA) 50 mg/L

Medium: urine

Time: end of shift

Parameter: Acetone (nonspecific)

(Contd. on page 3)

Safety Data Sheet

Printing date 01/25/2016

Revised On 01/25/2016

Trade name: GLOSS WHITE

(Contd. of page 2)

108-88-3 Toluene

BEI (USA)	0.02 mg/L Medium: blood Time: prior to last shift of workweek Parameter: Toluene
	0.03 mg/L Medium: urine Time: end of shift Parameter: Toluene
	0.3 mg/g creatinine Medium: urine Time: end of shift Parameter: o-Cresol with hydrolysis (background)

1330-20-7 xylene (mix)

BEI (USA)	1.5 g/g creatinine Medium: urine Time: end of shift Parameter: Methylhippuric acids
-----------	--

Hygienic protection:	Keep away from foodstuffs and animal feed. Wash hands after use. Immediately remove all soiled and contaminated clothing. Wash hands after use. Avoid contact with the eyes and skin. Do not eat or drink while working.
Breathing equipment:	A respirator is generally not necessary when using this product outdoors or in large open areas. In cases where short and/or long term overexposure exists, a charcoal filter respirator should be worn. If you suspect overexposure conditions exist, please consult an authority on chemical hygiene.
Hand protection:	Nitrile gloves.
Eye protection:	Protective gloves. The glove material must be impermeable and resistant to the substance. Tightly sealed goggles

9 Physical and chemical properties

Appearance:	Aerosol.
Odor:	Aromatic
Odor threshold:	Not determined.
pH-value:	Not determined.
Melting point/Melting range	Undetermined.
Boiling point:	-44 °C (-47 °F)
Flash point:	-19 °C (-2 °F)
Flammability (solid, gas):	Extremely flammable.
Decomposition temperature:	Not determined.
Auto igniting:	Product is not self-igniting.
Danger of explosion:	In use, may form flammable/explosive vapour-air mixture.
Lower Explosion Limit:	1.5 Vol %
Upper Explosion Limit:	10.9 Vol %
Vapor pressure:	Not determined.
Relative Density:	Between 0.77 and 0.85 (Water equals 1.00)
Vapour density	Not determined.
Evaporation rate	Not applicable.
Partition coefficient: n-octanol/water:	Not determined.
Solubility:	Not determined.
Viscosity:	Not determined.
VOC content:	574.5 g/l / 4.79 lb/gl
VOC content (less exempt solvents):	62.5 %
MIR Value:	1.38
Solids content:	13.0 %

10 Stability and reactivity

Reactivity:	Stable at normal temperatures.
Conditions to avoid:	Do not allow can to exceed 120 degrees Fahrenheit. Do not warehouse in subfreezing temperatures.
Chemical stability:	Not fully evaluated.
Possibility of hazardous reactions:	No dangerous reactions known.
Incompatible materials:	No further relevant information available.
Hazardous decomposition:	No dangerous decomposition products known.

11 Toxicological information**LD/LC50 values that are relevant for classification:****106-97-8 n-butane**

Inhalative | LC50/4 h | 658 mg/l (rat)

(Contd. on page 4)

Safety Data Sheet

Printing date 01/25/2016

Revised On 01/25/2016

Trade name: GLOSS WHITE

(Contd. of page 3)

13463-67-7 titanium dioxide

Oral	LD50	>20000 mg/kg (rat)
Dermal	LD50	>10000 mg/kg (rbt)
Inhalative	LC50/4 h	>6.82 mg/l (rat)

1330-20-7 xylene (mix)

Oral	LD50	8700 mg/kg (rat)
Dermal	LD50	2000 mg/kg (rbt)
Inhalative	LC50/4 h	6350 mg/l (rat)

Information on toxicological effects: No data available.**Skin effects:** Irritant to skin and mucous membranes.**Eye effects:** Irritating effect.**Sensitization:** No sensitizing effects known.**Carcinogenic categories****IARC (International Agency for Research on Cancer)**

108-88-3	Toluene	3
13463-67-7	titanium dioxide	2B
1330-20-7	xylene (mix)	3

NTP (National Toxicology Program)

None of the ingredients is listed.

12 Ecological information

Aquatic toxicity:	Hazardous for water, do not empty into drains.
Persistence and degradability:	The product is degradable after prolonged exposure to natural weathering processes.
Bioaccumulative potential:	No further relevant information available.
Mobility in soil:	No further relevant information available.
Other adverse effects:	No further relevant information available.

13 Disposal considerations

Dispose of in accordance with local, state, and federal regulations. Do not puncture, incinerate, or compact. Partially empty cans must be disposed of responsibly. Do not heat or cut empty containers with electric or gas torches.

Recommendation: Completely empty cans should be recycled.**14 Transport information**

UN-Number	UN1950
DOT	N/A
DOT	UN1950
ADR	Consumer Commodity ORM-D
Transport hazard class(es):	Aerosols, flammable
Class	1950 Aerosols
Marine pollutant:	2.1
Special precautions for user:	No
EMS Number:	Warning: Gases
Packaging Group:	F-D,S-U
UN "Model Regulation":	--
	UN1950, Aerosols, 2.1

15 Regulatory information**SARA Section 355 (extremely hazardous substances):**

None of the ingredients in this product are listed.

SARA Section 313 (Specific toxic chemical listings):

108-88-3	Toluene
1330-20-7	xylene (mix)

CPSC: This product complies with 16 CFR 1303 and does not contain more than 90 ppm of lead.**California Proposition 65 chemicals known to cause cancer:**

13463-67-7	titanium dioxide
100-41-4	ethyl benzene

California Proposition 65 chemicals known to cause developmental toxicity:

108-88-3 Toluene

CANADIAN ENVIRONMENTAL PROTECTION ACT:**WHMIS Symbols for Canada:**All hazardous ingredients for this product appear on the Canadian Domestic Substance List.
A - Compressed gas
D2A - Very toxic material causing other toxic effects**EPA:**

67-64-1	Acetone	I
108-88-3	Toluene	II

(Contd. on page 5)

Safety Data Sheet

Printing date 01/25/2016

Revised On 01/25/2016

Trade name: GLOSS WHITE

1330-20-7 xylene (mix)

(Contd. of page 4)

16 Other information

Contact: Regulatory Affairs
Date of preparation / last revision 01/25/2016 / -