

Specifications



Photo is representative

Eaton VMVL-3-J-R3-UNV1

Eaton Crouse-Hinds series Champ VMVL LED fixture, Cool white, 70W HID equivalent, No guard, Glass lens, 3000 lumens, 123 lm/W, Die cast aluminum, Stanchion 25° angled, Type III, 1-1/2" trade size, 100-277 Vac, 127-250 Vdc, 28W

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series Champ VMVL LED light fixture
CATALOG NUMBER	VMVL-3-J-R3-UNV1
UPC	662276893436
PRODUCT LENGTH/DEPTH	15.07 in
PRODUCT HEIGHT	12.85 in
PRODUCT WIDTH	11.62 in
PRODUCT WEIGHT	22.5 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION Hazardous/Classified Locations

Product specifications

LUMENS 3000

STANDARDS TYPE	NEC/CEC IEC IECEX/ATEX
NEC HAZARDOUS RATING	Class I, Division 2 Class I, Zone 2 Class II, Division 1 Class III
IECEX/ATEX HAZARDOUS RATING	Zone 21
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66

LUMENS PER WATT	123
COLOR TEMPERATURE	Cool white
MOUNTING METHOD	Stanchion 25° angled
TRADE SIZE	1-1/2"
OPTICAL DISTRIBUTION	Type III
GUARD TYPE	No guard
VOLTAGE RATING	100-277 Vac, 127-250 Vdc
FREQUENCY RATING	50/60 Hz
WATTAGE	28W
DIMMING	Dimmable driver
POWER FACTOR	> 0.90
EQUIVALENT LUMINAIRE	70W HID
MATERIAL	Die cast aluminum
LENS MATERIAL	Heat and impact resistant glass

Resources

3D MODELS

[SP3D Design Package - Champ VMVL LED Hazardous Area Light Fixtures](#)

BROCHURES

[Crouse-Hinds series Champ VMVL LED Luminaires - 3,000 to 13,000 lumens brochure](#)

[Crouse-Hinds series DLC approved lighting products](#)

[Crouse-Hinds series Global LED lighting portfolio](#)

CATALOGS

[Crouse-Hinds series Champ VMVL LED luminaires - 3,000 to 13,000 lumens catalog page](#)

INSTALLATION INSTRUCTIONS

[IF 1882 - Champ VMVL and PVML LED luminaires](#)

[IF 1888 - Champ VMVL and PVML Driver Replacement](#)

SPECIFICATIONS AND DATASHEETS

[Champ VMV LED Hazardous Area](#)

[Eaton Specification Sheet - VMVL-3-J-R3-UNV1](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative

Eaton VMVL-3-J-R3-UNV1

Eaton Crouse-Hinds series Champ VMVL LED fixture, Cool white, 70W HID equivalent, No guard, Glass lens, 3000 lumens, 123 lm/W, Die cast aluminum, Stanchion 25° angled, Type III, 1-1/2" trade size, 100-277 Vac, 127-250 Vdc, 28W

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series Champ VMVL LED light fixture
CATALOG NUMBER	VMVL-3-J-R3-UNV1
UPC	662276893436
PRODUCT LENGTH/DEPTH	15.07 in
PRODUCT HEIGHT	12.85 in
PRODUCT WIDTH	11.62 in
PRODUCT WEIGHT	22.5 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION Hazardous/Classified Locations

Product specifications

LUMENS 3000

STANDARDS TYPE	NEC/CEC IEC IECEX/ATEX
NEC HAZARDOUS RATING	Class I, Division 2 Class I, Zone 2 Class II, Division 1 Class III
IECEX/ATEX HAZARDOUS RATING	Zone 21
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66

LUMENS PER WATT	123
COLOR TEMPERATURE	Cool white
MOUNTING METHOD	Stanchion 25° angled
TRADE SIZE	1-1/2"
OPTICAL DISTRIBUTION	Type III
GUARD TYPE	No guard
VOLTAGE RATING	100-277 Vac, 127-250 Vdc
FREQUENCY RATING	50/60 Hz
WATTAGE	28W
DIMMING	Dimmable driver
POWER FACTOR	> 0.90
EQUIVALENT LUMINAIRE	70W HID
MATERIAL	Die cast aluminum
LENS MATERIAL	Heat and impact resistant glass

Resources

3D MODELS

[SP3D Design Package - Champ VMVL LED Hazardous Area Light Fixtures](#)

BROCHURES

[Crouse-Hinds series Champ VMVL LED Luminaires - 3,000 to 13,000 lumens brochure](#)

[Crouse-Hinds series DLC approved lighting products](#)

[Crouse-Hinds series Global LED lighting portfolio](#)

CATALOGS

[Crouse-Hinds series Champ VMVL LED luminaires - 3,000 to 13,000 lumens catalog page](#)

INSTALLATION INSTRUCTIONS

[IF 1882 - Champ VMVL and PVML LED luminaires](#)

[IF 1888 - Champ VMVL and PVML Driver Replacement](#)

SPECIFICATIONS AND DATASHEETS

[Champ VMV LED Hazardous Area](#)

[Eaton Specification Sheet - VMVL-3-J-R3-UNV1](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

