



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## WSPPEMUNV Sensor Hubbell BLDG Automation

Catalog Number	WSPPEMUNV
Manufacturer	Hubbell BLDG Automation
Description	N/A Passive Infrared and Photocell, N/A, Voltage Rating: Line Voltage, 120 V-277 V and Low Voltage, 24 VDC, Operating Temperature: -40 to 149 °F and -40 to 65 °C, Mounting Type: High Mount and Low Mount and End Mount and Fixture Mount, Environmental Conditions: Indoor and Outdoor and Low Temperature (-40° C), Color: White, Compliance: Buy American 52.225-9 and Buy American (Taa) 52.225-11 and Ip65
Weight per unit	0.4400 (lbs/each)
Product Category	Lighting Occupancy Sensors

### Features

supply voltage	120-480;Low Voltage
Voltage Rating	Line Voltage, 120 V-277;Low Voltage, 24

### Descriptions

Description	SENSOR
extra long description	HBA WSPPEMUNV WSPPII HBAY SNSR END MN
Long Description	N/A Passive Infrared and Photocell, N/A, Voltage Rating: Line Voltage, 120 V-277 V and Low Voltage, 24 VDC, Operating Temperature: -40 to 149 °F and -40 to 65 °C, Mounting Type: High Mount and Low Mount and End Mount and Fixture Mount, Environmental Conditions: Indoor and Outdoor and Low Temperature (-40° C), Color: White, Compliance: Buy American 52.225-9 and Buy American (TAA) 52.225-11 and IP65
Product Type	Wspii Hbay SNSR End MNT Unv

### Manufacturer Information

Brand	NX Lighting Controls
GTIN	00640181200839
Manufacturers Part Number	WSPPEMUNV
UPC	640181200839

### Taxonomies, Classifications, and Categories

Category Description	Emergency & Exit Lighting
Type	Controls;Sensors

### Packaging

Carton	1
Weight Per each	0.44



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Cold Storage;Garages;Gymnasiums;Manufacturing Floors;Parking Lots;Site/Area;Warehouses
environmental conditions	Indoor;Low Temperature (-40° C);Outdoor
Mounting	End Mount;Fixture Mount;High Mount;Low Mount