



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WSPPEMUNV Sensor *Hubbell BLDG Automation*

Catalog Number	WSPPEMUNV
Manufacturer	Hubbell BLDG Automation
Description	N/A Passive Infrared and Photocell, N/A, Voltage Rating: Line Voltage, 120 V-277 V and Low Voltage, 24 VDC, Operating Temperature: -40 to 149 °F and -40 to 65 °C, Mounting Type: High Mount and Low Mount and End Mount and Fixture Mount, Environmental Conditions: Indoor and Outdoor and Low Temperature (-40° C), Color: White, Compliance: Buy American 52.225-9 and Buy American (Taa) 52.225-11 and Ip65
Weight per unit	0.4400 (lbs/each)
Product Category	Lighting Occupancy Sensors

Features

supply voltage	Low Voltage;120-480
Voltage Rating	Line Voltage, 120 V-277;Low Voltage, 24

Material, Color, and Finish

Color	White
-------	-------

Descriptions

Description	SENSOR
extra long description	HBA WSPPEMUNV WSPPI HBAY SNSR END MN
Long Description	N/A Passive Infrared and Photocell, N/A, Voltage Rating: Line Voltage, 120 V-277 V and Low Voltage, 24 VDC, Operating Temperature: -40 to 149 °F and -40 to 65 °C, Mounting Type: High Mount and Low Mount and End Mount and Fixture Mount, Environmental Conditions: Indoor and Outdoor and Low Temperature (-40° C), Color: White, Compliance: Buy American 52.225-9 and Buy American (TAA) 52.225-11 and IP65
Product Type	Wspii Hbay SNSR End MNT Unv

Manufacturer Information

Brand	NX Lighting Controls
GTIN	00640181200839
Manufacturers Part Number	WSPPEMUNV
UPC	640181200839

Taxonomies, Classifications, and Categories

Category Description	Emergency & Exit Lighting
Type	Sensors;Controls



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.44

Uses, Certifications, and Standards

Application	Garages;Gymnasiums;Cold Storage;Parking Lots;Manufacturing Floors;Site/Area;Warehouses
environmental conditions	Indoor;Outdoor;Low Temperature (-40 ° C)
Mounting	High Mount;Low Mount;End Mount;Fixture Mount
Operating Temperature	-40 to 149